



### Nameplate Specifications

Output HP	1.0 Hp	Output KW	0.75 kW
Frequency	60 Hz	Voltage	230/460 V
Current	3.0/1.5 A	Speed	1745/1425 rpm
Service Factor	1.25	Phase	3
Duty	Continuous	Insulation Class	B
Frame	P143JP	Enclosure	Drip Proof
Thermal Protection	None	Ambient Temperature	40 °C
UL	No	CSA	Y
Number of Speeds	1		

### Technical Specifications

Electrical Type	Polyphase, Induction Type, Single Or Dual Voltage	Starting Method	Across The Line
Poles	4	Rotation	Reversible Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	19.49 in
Frame Length	8.00 in	Shaft Diameter	1.156 in
Shaft Extension	7.344 in		
Connection Drawing	18304024.PCX	Outline Drawing	E118E-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/11/2021