

**Nameplate Specifications**

Output HP	3.0 Hp	Output KW	2.2 kW
Frequency	60 Hz	Voltage	200 V
Current	8.9 A	Speed	1760 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	S182T	Enclosure	Drip Proof
Thermal Protection	None	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

**Technical Specifications**

Electrical Type	Three Phase	Starting Method	Across The Line
Poles	4	Rotation	Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	13.65 in
Frame Length	8.00 in	Shaft Diameter	1.125 in
Shaft Extension	2.86 in		
Outline Drawing	18709201-001-S01		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021