

PRODUCT INFORMATION PACKET



Model No: E372M2A

Catalog No: E372M2A

10 HP Close-Coupled Pump Motor, 3 phase, 3600 RPM, 230/460 V, 213JP Frame, ODP
Close-Coupled Pump Motors



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E






Nameplate Specifications

Output HP	10 Hp	Output KW	7.5 kW
Frequency	60 Hz	Voltage	230/460 V
Current	24.2/12.1 A	Speed	3515 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	213JP	Enclosure	Drip Proof
Thermal Protection	No	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
Number of Speeds	1		

Technical Specifications

Electrical Type	Polyphase	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	JP	Overall Length	23.03 in
Frame Length	11.15 in	Shaft Diameter	1.750 in
Shaft Extension	8.12 in		
Connection Drawing	A-EE7308_CY	Outline Drawing	ss86594


This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021



DASH	FR.	C	AG	BS	MOUNTING
965	213JP	21.53	13.41	5.43	
1115	213/15JP	23.03	14.91	6.93	
1240	213/15JP	24.28	16.16	8.18	F1 ONLY

NOTES:


1. NAMEPLATE TO BE READ FROM C'BOX SIDE OF MOTOR.
2. BOX CAN BE MOUNTED IN 90° STEPS.
3. BOX CAN BE MOUNTED ON OPPOSITE SIDE BY REMOVING BRACKETS AND TURNING FRAME 180°. (EXCEPT AS NOTED)

6	TITLE BLOCK LOGO CHANGE PER ECO-0078542	MDV 06/09/2015		TOLERANCES UNLESS SPECIFIED		 Regal Beloit America, Inc.	DRAWN DA 03-26-1996			
5	WHEN REQ'D NOTE ADDED PER ECO-0043948	UD 01/20/14	GR	DEC.	INCHES		CHK ML 04-01-1996			
4	UPDATED DRAWING	TJW 04/27/2007		.X	±.1		APPD DN 04-01-1996			
3	REDRAWN IN AUTOCAD	TAT 07-13-2004	ML	.XX	±.03	TITLE OUTLINE 210JP FR.-BB-TS-DR.PR.-C' FACE	SCALE 1=5			
2	UPDATED C'BOX GEOMETRY CN 28425	DRS 01-31-2000		.XXX	±.005		REF			
1	NEW DRAWING - DES/DEV	DA 04-02-1996		.XXXX	±.0005	MAT'L.	FMF			
NO.	REVISION	BY & DATE	CHK	ANG	±7'30"	FINISH	PREV			
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT			RFP		CAD FILE ss86594		SIZE A	DRAWING NO. SS86594	PAGE OF	REV. 6
			DIST LB							



THREE PHASE DUAL VOLTAGE MOTOR

EE7308-CY

HIGH VOLTAGE



LOW VOLTAGE




VIEW OF TERMINAL END

REF.
WINDING DIAGRAM

T8Y, T2Y, T2BL, T4BX, T2EC, T2G
T6BZ, T2B, T6BL, T4AV, T6B, T4B

OPTIONAL CORD CONNECTION

L1 _____ WHITE _____
L2 _____ RED _____
L3 _____ BLACK _____

			TOLERANCES UNLESS SPECIFIED			DRAWN GR 03/08/12	
			DEC.	INCHES		CHK ST 03/08/12	
			.X	±.1		APPD	
			.XX	±.02		SCALE 1=1	
			.XXX	±.005		REF EE7308	
1	DRAWING PART NUM UPDATED	GR 09/07/12	SR	.XXXX ±.0005	MAT'L.	FMF	
NO.	REVISION	BY & DATE	CHK	ANG ±7'30"	FINISH	PREV	
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT			RFP	CAD FILE EE7308-CY		SIZE A	DRAWING NO. EE7308-CY
			DIST WP				PAGE OF 1