

PRODUCT INFORMATION PACKET



Model No: E372M2
Catalog No: E372M2

Close-Coupled Pump Motor, 10 HP, 3 Ph, 60 Hz, 208-230/460 V, 3600 RPM, 213JP Frame, DP



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications


Output HP	10 Hp	Output KW	7.5 kW
Frequency	60 Hz	Voltage	208-230/460 V
Current	26-23.4/11.7 A	Speed	3515 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	213JP	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
Number of Speeds	1		

Technical Specifications

Electrical Type	Polyphase	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	23.03 in
Frame Length	11.15 in	Shaft Diameter	1.750 in
Shaft Extension	8.12 in		
Connection Drawing	80022802	Outline Drawing	SS86594CY

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/28/2022

SS86594CY



NOTES:

1. NAMEPLATE TO BE READ FROM C'BOX SIDE OF MOTOR.
2. BOX CAN BE MOUNTED IN 90° STEPS.
3. BOX CAN BE MOUNTED ON OPPOSITE SIDE BY REMOVING BRACKETS AND TURNING FRAME 180°. (EXCEPT AS NOTED)

DASH	FR.	C	AG	BS	MOUNTING
965	213JP	21.53	13.41	5.43	
1115	213/15JP	23.03	14.91	6.93	
1240	213/15JP	24.28	16.16	8.18	F1 ONLY

				TOLERANCES UNLESS SPECIFIED		Century®	DRAWN GR 09/03/12		
				DEC.	INCHES		CHK SR 09/03/12	APPD	
				.X	±.1	TITLE OUTLINE 210JP FR.-BB-TS-DR.PR.-C' FACE	SCALE	1=5	
				.XX	±.03		REF	SS86594	
				.XXX	±.005		FMF		
				.XXXX	±.0005		PREV		
NO.	REVISION	BY & DATE	CHK	ANG	±7'30"		FINISH		
				RFP		CAD FILE	SS86594CY	SIZE	DRAWING NO. PAGE OF REV.
				DIST	LB			A	SS86594CY

THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT