



### Nameplate Specifications

Phase	3	Output HP	1.5 Hp
Output KW	1.1 kW	Voltage	208-230/460 V
Speed	1740 rpm	Service Factor	1.15
Frame	145JP	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	86.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	4.3-3.90/1.95 A	Duty	Continuous
Insulation Class	F	UL	Recognized
CSA	Y	CE	Y
Number of Speeds	1		

### Technical Specifications

Electrical Type	POLYPHASE	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	Keyed	Overall Length	19.70 in
Frame Length	6.75 in	Shaft Diameter	1.156 in
Shaft Extension	7.31 in		
Connection Drawing	A-EE7308	Outline Drawing	CPE15-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:05/15/2023