



Nameplate Specifications

Output HP	15 Hp	Output KW	11.2 kW
Frequency	60 Hz	Voltage	230/460 V
Current	34/17 A	Speed	3525 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	215JP	Enclosure	Drip Proof
Thermal Protection	No	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
Number of Speeds	1		

Technical Specifications

Electrical Type	Polyphase	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	JP	Overall Length	23.03 in
Frame Length	11.15 in	Shaft Diameter	1.750 in
Shaft Extension	8.12 in		
Connection Drawing	005010.01	Outline Drawing	ss86594

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021