

# PRODUCT INFORMATION PACKET



Model No: E368M2

Catalog No: E368M2

7.5 HP Close-Coupled Pump Motor, 3 phase, 1800 RPM, 208-230/460 V, 213JM Frame, ODP  
Close-Coupled Pump Motors



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E







### Nameplate Specifications

Output HP	7.5 Hp	Output KW	5.6 kW
Frequency	60 Hz	Voltage	208-230/460 V
Current	21-19.2/9.6 A	Speed	1760 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	213JM	Enclosure	Drip Proof
Thermal Protection	No	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	1

### Technical Specifications


Electrical Type	Polyphase	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	20.41 in
Frame Length	12.40 in	Shaft Diameter	1.250 in
Shaft Extension	4.25 in		
Outline Drawing	SS86566CY	Connection Drawing	80022802

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021



DASH	FR.	C	AG	BS	MOUNTING
965	213/215JM	17.66	13.41	5.43	F1 ONLY
1115	213/215JM	19.16	14.91	6.93	F1/F2
1240	213/215JM	20.41	16.16	8.18	F1 ONLY

- NOTES:
- NAMEPLATE TO BE READ FROM C'BOX SIDE OF MOTOR.
  - BOX CAN BE MOUNTED IN 90° STEPS.
  - BOX CAN BE MOUNTED ON OPPOSITE SIDE BY REMOVING BRACKETS AND TURNING FRAME 180° (EXCEPT AS NOTED)

				TOLERANCES UNLESS SPECIFIED			DRAWN GR 07/19/12				
				DEC.	INCHES		CHK SS 07/19/12				
				.X	±.1		APPD				
				.XX	±.03		SCALE 1=5				
				.XXX	±.005		REF SS86566				
A	F1/F2 NOTE UPDATED IN TABLE		GR 12/14/12	SR	.XXXX ±.0005	MAT'L.			FMF		
NO.	REVISION		BY & DATE	CHK	ANG ±7'30"	FINISH			PREV		
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT – DO NOT SCALE THIS PRINT				RFP		CAD FILE SS86566CY		SIZE	DRAWING NO.	PAGE OF	REV.
				DIST LB				A	SS86566CY		A