



### Nameplate Specifications

|                    |             |                     |            |
|--------------------|-------------|---------------------|------------|
| Output HP          | 10 Hp       | Output KW           | 7.5 kW     |
| Frequency          | 60 Hz       | Voltage             | 230/460 V  |
| Current            | 24.2/12.1 A | Speed               | 3515 rpm   |
| Service Factor     | 1.15        | Phase               | 3          |
| Duty               | Continuous  | Insulation Class    | F          |
| Frame              | 213JP       | Enclosure           | Drip Proof |
| Thermal Protection | No          | Ambient Temperature | 40 °C      |
| UL                 | Recognized  | CSA                 | Y          |
| Number of Speeds   | 1           |                     |            |

### Technical Specifications

|                       |             |                   |                 |
|-----------------------|-------------|-------------------|-----------------|
| Electrical Type       | Polyphase   | Starting Method   | Across The Line |
| Poles                 | 2           | Rotation          | Reversible      |
| Mounting              | Rigid Base  | Drive End Bearing | Ball            |
| Opp Drive End Bearing | Ball        | Frame Material    | Rolled Steel    |
| Shaft Type            | JP          | Overall Length    | 23.03 in        |
| Frame Length          | 11.15 in    | Shaft Diameter    | 1.750 in        |
| Shaft Extension       | 8.12 in     |                   |                 |
| Connection Drawing    | A-EE7308_CY | Outline Drawing   | ss86594         |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021