

Nameplate Specifications

Output HP	10.0 Hp	Output KW	7.5 kW
Frequency	60 Hz	Voltage	230/460 V
Current	23.2/11.6 A	Speed	3495 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	213JP	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
Number of Speeds	1		

Technical Specifications

Electrical Type	Three Phase	Starting Method	Across The Line
Poles	2	Rotation	Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	23.78 in
Frame Length	11.00 in	Shaft Diameter	1.375 in
Shaft Extension	8.12 in		
Outline Drawing	E372ME-S01	Connection Drawing	80022802.PCX

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/16/2022