



Nameplate Specifications

| | | | |
|--------------------|---------------|---------------------|------------|
| Output HP | 10 Hp | Output KW | 7.5 kW |
| Frequency | 60 Hz | Voltage | 230/460 V |
| Current | 24.2/12.1 A | Speed | 3530 rpm |
| Service Factor | 1.15 | Phase | 3 |
| Duty | Continuous | Insulation Class | F |
| Frame | 213T | Enclosure | Drip Proof |
| Thermal Protection | No Protection | Ambient Temperature | 40 °C |
| UL | Recognized | CSA | Y |
| CE | Y | Number of Speeds | 1 |

Technical Specifications

| | | | |
|-----------------------|-------------|-------------------|-----------------|
| Electrical Type | Polyphase | Starting Method | Across The Line |
| Poles | 2 | Rotation | Reversible |
| Mounting | Rigid Base | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Rolled Steel |
| Shaft Type | T | Overall Length | 17.30 in |
| Frame Length | 11.15 in | Shaft Diameter | 1.375 in |
| Shaft Extension | 3.47 in | | |
| Connection Drawing | A-EE7308_CY | Outline Drawing | ss86500 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/28/2022