

## Nameplate Specifications

Phase	3	Output HP	0.3352555 Hp
Output KW	0.25 kW	Voltage	230/400 V
Speed	2858 rpm	Service Factor	1
Frame	63B	Enclosure	Totally Enclosed Fan Cooled
Efficiency	70.1 %	Ambient Temperature	40 °C
Frequency	50 Hz	Power Factor	0.6
Duty	S1	Insulation Class	F
Drive End Bearing Size	6202	Opp Drive End Bearing Size	6202
UL	No	CSA	No
CE	Yes	IP Code	IP55
Number of Speeds	1		

## Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	2	Rotation	Bi-Directional
Mounting	B35	Motor Orientation	Horizontal
Drive End Bearing	Zz	Opp Drive End Bearing	Zz
Frame Material	Cast Iron	Shaft Type	Keyed
Overall Length	275.50 mm	Frame Length	105.00 mm
Shaft Diameter	11.000 mm	Shaft Extension	23 mm
Assembly/Box Mounting	Top		
Connection Drawing	SC-01-T-1v-1a	Outline Drawing	B3A048060001D01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/10/2023