

PRODUCT INFORMATION PACKET

Model No: E3AB3004137B30D41100

Catalog No: E3AB3004137B30D41100

Made in Italy E3AB30 Series, General Purpose Low Voltage IEC motor IE3, Flameproof, 11,00kW,
3 phase, 1476 RPM, D400/Y690V 50Hz, 132ML Frame B3, 4 Poles, IC411, Higher Output Motor



Regal and CEMP are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E






Nameplate Specifications

Output HP	15 Hp	Output KW	11.0 kW
Frequency	50 Hz	Voltage	400/690 V
Current	20.7 A	Speed	1476 rpm
Service Factor	1	Phase	3
Efficiency	91.4 %	Power Factor	0.84
Duty	S1	Insulation Class	F
Frame	132ML	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6308	Opp Drive End Bearing Size	6308
UL	No	CSA	No
CE	Yes	IP Code	IP55
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	4	Rotation	Bi-Directional
Mounting	B3	Motor Orientation	Horizontal
Drive End Bearing	Zz C3	Opp Drive End Bearing	Zz C3
Frame Material	Cast Iron	Shaft Type	Keyed
Overall Length	728.00 mm	Frame Length	365.00 mm
Shaft Diameter	38.000 mm	Shaft Extension	80 mm
Assembly/Box Mounting	Top		
Connection Drawing	SC-01-T-1v-1a	Outline Drawing	B3A04E8133001A01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:12/02/2022



CUSTOMER REFERENCE AND ADDITIONAL INFORMATION:

MOTOR TYPE AND DESCRIPTION:

DRAWING REVISION	REVISION BY	DATE	TOLERANCES (EXCEPT AS NOTED) TOLERANCES: ±2 * TOLERANCES: ±0.8 DIMENSIONS ARE IN mm ACCORDING TO IEC 60072	DRAWN BY LP	 		
ECO	APPROVED BY	DATE		DATE 18/02/2021			
ECO DESCRIPTION				APPROVED BY MG	DESCRIPTION Motor A132 LA/LB (L) B3 Simplified		
COPYRIGHT CEMP Srl. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF CEMP Srl. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.				DATE 19/02/2021			
			SERIAL NUMBER	REFERENCE	SIZE A4 		


Schema di collegamento - *Connection diagram*
Schemas de branchement - *Schaltplän*
Esquemas de conexión




DTE 01/01/2004
SC - 01 - T - 1v.doc

**Motori trifase una velocità - *Single speed, three phase motors* - Moteurs triphasé une vitesse
Drehstrommotor Eine Drehzahlstufe - Motores trifásico una velocidad**

Collegamento - *Connection* - Connexion - *Schaltung* - Conexión



Collegamento - *Connection* - Connexion - *Schaltung* - Conexión



L1 - L2 - L3 = Linea - *Supply* - Reseau - *Netz* - Red

Per invertire la rotazione invertire due fasi - *To change the rotation reverse two phases* - Pour changer le sens de rotation inverser deux phases - *Zur Drehrichtungsänderung zwei Phasen vertauschen* - Para invertir el sentido de rotación invertir dos fases

Marcatura Morsetti Ausiliari - <i>Additional terminals marking (IEC60034-8)</i>		
Marcatura <i>Marking</i>	No. morsetti <i>terminals</i>	Morsetto ausiliare per: <i>Additional terminal for:</i>
TP1A - TP2A (allarme- <i>warning</i>)	2	Termistori PTC (alta velocità) - <i>Thermistor PTC (high speed) [*]</i>
TP1B - TP2B (allarme- <i>warning</i>)	2	Termistori PTC (bassa velocità) - <i>Thermistor PTC (low speed) [*]</i>
R1 - R2 - R3 (I sensore - <i>sensor</i>)	3	Termistore PT100 3 fili - <i>Thermistor PT 100 with 3 wires</i>
R4 - R5 - R6 (II sensore - <i>sensor</i>)	3	
R7 - R8 - R9 (III sensore - <i>sensor</i>)	3	
R11 - R12 - R13 (anteriore - <i>DE</i>)	3	Termistore PT100 su cuscinetto - <i>Thermistor PT 100 on bearing</i>
R21 - R22 - R23 (posteriore - <i>NDE</i>)	3	
TB1 - TB2 (allarme- <i>warning</i>)	2	Protettore bimetallico normalmente chiuso - <i>Normally closed bi-metallic switch (**)</i>
TB3 - TB4 (intervento- <i>switch off</i>)	2	Protettore bimetallico del freno normalmente chiuso - <i>NC brake bi-metallic switch (**)</i>
TB8 - TB9 (intervento- <i>switch off</i>)	2	
TM1 - TM2 (allarme- <i>warning</i>)	2	Protettore bimetallico normalmente aperto - <i>Normally open bi-metallic switch (**)</i>
TM3 - TM4 (intervento- <i>switch off</i>)	2	
HE1- HE2	2	Resistenze riscaldanti - <i>Space heaters</i>
U1 - U2	2	Ventilazione ausiliaria monofase - <i>Single phase forced ventilation</i>
U - V - W	2	Ventilazione ausiliaria trifase - <i>Three phase forced ventilation</i>
colori secondo schema del produttore - <i>colours according manufacturer</i>	9	Encoder
CA1 - CA2	2	Condensatore - <i>Capacitor</i>
PE	1	Conduttore di terra - <i>Earth cable</i>

[*] U nominale - *U rated* = 6V - max 30V

(**) U nominale - *U rated* = 250V



FOGLIO DATI PER MOTORI ELETTRICI ASINCRONI TRIFASI : SERIE IEC
DATA SHEET FOR ASYNCHRONOUS THREEPHASE INDUCTION MOTORS: IEC SERIES

Cliente / Customer	CEMP
Offerta / Offer : 2021.	
Impianto / Plant	-

DATI DI PROGETTO - DESIGN DATA

Modo di protezione	II2G	Motore / Frame
Type of protection		Scatola morsetti / Terminal box
Tem. Amb. Min. / Min Amb.Temp.	-20	°C
Umidità relativa / Relative humidity	90%	
Tensione nominale / Rated Voltage	400 V ± 5%	

Ex db IIB T4 Gb	IP55
Ex db IIB Gb	IP55
Tem. Amb. Max. / Max Amb. Temp.	40 °C
Altitudine / Altitude	< 1000 mslm / masl
Frequenza / Frequency	50 Hz ± 2%

DATI FUNZIONALI E COSTRUTTIVI - PERFORMANCE AND CONSTRUCTION DATA

1	Quantità / Quantity		01
2	Motore tipo / Motor type		E3AB30 132ML 4
3	Numero di serie / Serial Number		-
4	Forma costruttiva / Shape		B3
5	Certificato / Certificate	TÜV CY	17 ATEX 0205845 X
6	Altro certificato / Other certificate		
Dati nominali / Rated data			
7	Poli / Pole	n°	4
8	Potenza nominale / Rated power	kW	11,00
9	Corrente nominale / Rated current	A	20,66
10	Velocità nominale / Full Load speed	1/min	1476
11	Collegamento / Winding connection		D
12	Isolamento / Insulation class		F
13	Sovratemperatura / Temperature rise		80K
14	Raffreddamento / Cooling type		IC411
15	Fattore di servizio / Service factor		1
16			
17	Classe di rendimento / Efficiency level	IEC 34-30	IE3
Performances elettriche / Electrical performances			
Carico / Load		4/4	3/4
18	Giri / Speed	1/min	1476
19	Corr. / Curr.	A	20,66
20	Rend / Eff	%	91,4
21	cos φ	-	0,84
Performances all'avviamento / Starting performances			
22	Ia/In - LRC/FLC	%	735
23	Cosphi a rotore bloccato / LR power factor		0,47
	Tempo a rotore bloccato / LRWT		
24	100% Un (A caldo / Warm)	sec	9
25	(A freddo / Cold)	sec	24
26	80% Un (A caldo / Warm)	sec	14
27	(A freddo / Cold)	sec	38
	Tempo di avviamento ammissibile / ART		
28	100% Un	sec	21
29	80% Un	sec	33
Curva di coppia / Speed-torque values			
30	Coppia nominale / Rated Torque	Nm	71,17
31	Ca/Cn - LRT/FLT	%	240
32	Cmax/Cn - BDT/FLT	%	320
33			
34			
35			
Varie / Other			
36			
37			
38			
39			

Servizio / Duty		
40	Servizio / Duty type	S1
41	Intermittenza / Cyclic duration factor	-
42	Avviamenti-ora / Starting-hour	-
43	Tempo ciclo / Time	-
Cuscinetti / Bearings		
44	Cuscinetto ant / DE bearing	6308 ZZ C3
45	Cuscinetto post / NDE bearing	6308 ZZ C3
46	Carico radiale max / Max radial load in X1	1910
47	Carico assiale max / Max axial load	590
48	Tipo grasso / Grease type	LGHP2 SKF or equivalent
49	Intervallo lubrificazione / Lubrication	h
50	Quantità grasso / Quantity grease	gr
Caratteristiche meccaniche / mechanical specification		
51	Massa / Mass	kg
52	Momento d'inerzia / Moment of inertia	kgm2
53	Rumore a vuoto / Noise at no load (1 m)	Lp dB(A)
54	Vibrazioni / Vibration level	IEC 34-14
55	Limite norma / Vibration limit	mm/sec
56		
57		
Dati entrata cavi - verniciatura / Cable entry and painting		
63	Entrata cavi / Cable entry	2xM32
64	Ciclo verniciatura / Painting cycle	STD
65	Colore finale / Final colour	RAL
66		
67		
68		
69		
70		
71		
Ausiliari - Auxiliaries		
72	Sonde termiche / Temperature detector	winding
73	Sonde termiche / Temperature detector	bearing
74	Scaldiglie / Heaters	V / W
75	Preparation for SPM sensor	-
76	Pressacavi / Cable glands	NO
77		

CURVA COPPIA/CORRENTE-GIRI TORQUE/CURRENT-SPEED DIAGRAM

Cliente / Customer CEMP

 Impianto / Plant -
 ITEM -

 Numero d'offerta / Offer Number 2021.
 -

Motore / Motor E3AB30 132ML 4

Potenza nominale / Rated power 11,00 kW

Poli / Pole 4


Tensione - Frequenza / Voltage - Frequency 400 - 50 V - Hz

Corrente / Rated current 20,66 A

Velocità / Speed 1476 rpm

Coppia / Torque 71,17 Nm

— COPPIA - TORQUE — CORRENTE - CURRENT



Valori calcolati - Data obtained by calculation method

CURVA COPPIA/CORRENTE-GIRI (Tensione ridotta)
TORQUE/CURRENT-SPEED DIAGRAM (Reduced voltage)

Cliente / Customer CEMP

Impianto / Plant -
ITEM -

Numero d'offerta / Offer Number 2021.
-

Motore / Motor E3AB30 132ML 4

Potenza nominale / Rated power 11,00 kW

Poli / Pole 4


Tensione - Frequenza / Voltage - Frequency 400 - 50 V - Hz

Corrente / Rated current 20,66 A

Velocità / Speed 1476 rpm

Coppia / Torque 71,17 Nm

— COPPIA - TORQUE — CORRENTE - CURRENT
- - - COPPIA - TORQUE 80% Un - - - CORRENTE - CURRENT 80% Un



Valori calcolati - Data obtained by calculation method

CURVE CARATTERISTICHE PERFORMANCE CURVES

Cliente / Customer

CEMP

Impianto / Plant

-

ITEM

-

Numero d'offerta / Offer Number

2021.

-

Motore / Motor

E3AB30 132ML 4

Potenza nominale / Rated power

11,00

kW

Poli / Pole

4

Tensione - Frequenza / Voltage - Frequency

400 - 50

V - Hz

Corrente / Rated current

20,66

A

Velocità / Speed


1476

rpm

Coppia / Torque

71,17


Nm



Valori calcolati - Data obtained by calculation method

CURVA LIMITE CORRENTE TEMPO
THERMAL WITHSTAND CURVE

Cliente / Customer	CEMP	
Impianto / Plant	-	
ITEM	-	
Numero d'offerta / Offer Number	2021.	
	-	
Motore / Motor	E3AB30 132ML 4	
Potenza nominale / Rated power	11,00	kW
Poli / Pole	4	
Tensione - Frequenza / Voltage - Frequency	400 - 50	V - Hz
Corrente / Rated current	20,66	A
Velocità / Speed	1476	rpm
Coppia / Torque	71,17	Nm



Valori calcolati - Data obtained by calculation method

Data / Date 28 January 2022

CURVA LIMITE CORRENTE TEMPO (Tensione ridotta)
THERMAL WITHSTAND CURVE (Reduced voltage)

Cliente / Customer CEMP


Impianto / Plant -
ITEM -

Numero d'offerta / Offer Number 2021.
-

Motore / Motor E3AB30 132ML 4

Potenza nominale / Rated power	11,00	kW
Poli / Pole	4	
Tensione - Frequenza / Voltage - Frequency	400 - 50	V - Hz
Corrente / Rated current	20,66	A
Velocità / Speed	1476	rpm
Coppia / Torque	71,17	Nm

— COLD (100% Un) — HOT (100% Un) - - COLD (80% Un) - - HOT (80% Un)



Valori calcolati - Data obtained by calculation method