

PRODUCT INFORMATION PACKET

Model No: E3AB3004207B50D41100

Catalog No: E3AB3004207B50D41100

Made in Italy E3AB30 Series, General Purpose Low Voltage IEC motor IE3, Flameproof, 37,00kW,
3 phase, 1483 RPM, D400/Y690V 50Hz, 200LBX Frame B5, 4 Poles, IC411, Higher Output Motor



Regal and CEMP are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E


Nameplate Specifications

Output HP	50 Hp	Output KW	37.0 kW
Frequency	50 Hz	Voltage	400/690 V
Current	67.2 A	Speed	1483 rpm
Service Factor	1	Phase	3
Efficiency	93.9 %	Power Factor	0.85
Duty	S1	Insulation Class	F
Frame	200LBX	Enclosure	Totally Enclosed Fan Cooled
Ambient Temperature	40 °C	Drive End Bearing Size	6312
Opp Drive End Bearing Size	6312	UL	No
CSA	No	CE	Yes
IP Code	IP55	Number of Speeds	1

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	4	Rotation	Bi-Directional
Mounting	B5	Motor Orientation	Horizontal
Drive End Bearing	Zz C3	Opp Drive End Bearing	Zz C3
Frame Material	Cast Iron	Shaft Type	Keyed
Overall Length	1060.00 mm	Frame Length	525.00 mm
Shaft Diameter	55.000 mm	Shaft Extension	110 mm
Assembly/Box Mounting	Top		
Outline Drawing	B5A04E8200001B01	Connection Drawing	SC-01-T-1v-1a

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:12/02/2022



MOTOR TYPE AND DESCRIPTION:

DRAWING REVISION	REVISION BY	DATE	TOLERANCES (EXCEPT AS NOTED) TOLERANCES: ± 2 * TOLERANCES: ± 0.8	DRAWN BY LP	 		
ECO	APPROVED BY	DATE	DIMENSIONS ARE IN mm ACCORDING TO IEC 60072	DATE 27/12/2016	DESCRIPTION Motor A200 LB/LC (L) B5 IE3		
ECO DESCRIPTION				APPROVED BY DP			
				DATE 27/12/2016			
				REFERENCE			
COPYRIGHT CEMP Srl. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF CEMP Srl ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.			SERIAL NUMBER	FIRST ANGLE PROJECTION 	SIZE A4	DRAWING NUMBER B5A04E8200001B01	SHEET 1 OF 2

Schema di collegamento - *Connection diagram*
Schemas de branchement - *Schaltpl n*
Esquemas de conexi n



DTE 01/01/2004
SC - 01 - T - 1v.doc

**Motori trifase una velocit  - *Single speed, three phase motors* - Moteurs triphas  une vitesse
Drehstrommotor Eine Drehzahlstufe - Motores trif sico una velocidad**

Collegamento - *Connection* - Connexion - *Schaltung* - Conexi n



Collegamento - *Connection* - Connexion - *Schaltung* - Conexi n



L1 - L2 - L3 = Linea - *Supply* - Reseau - *Netz* - Red

Per invertire la rotazione invertire due fasi - *To change the rotation reverse two phases* - Pour changer le sens de rotation inverser deux phases - *Zur Drehrichtungs nderung zwei Phasen vertauschen* - Para invertir el sentido de rotaci n invertir dos fases

Marcatura Morsetti Ausiliari - <i>Additional terminals marking (IEC60034-8)</i>		
Marcatura <i>Marking</i>	No. morsetti <i>terminals</i>	Morsetto ausiliare per: <i>Additional terminal for:</i>
TP1A - TP2A (allarme- <i>warning</i>)	2	Termistori PTC (alta velocità) - <i>Thermistor PTC (high speed) [*]</i>
TP1B - TP2B (allarme- <i>warning</i>)	2	Termistori PTC (bassa velocità) - <i>Thermistor PTC (low speed) [*]</i>
R1 - R2 - R3 (I sensore - <i>sensor</i>)	3	Termistore PT100 3 fili - <i>Thermistor PT 100 with 3 wires</i>
R4 - R5 - R6 (II sensore - <i>sensor</i>)	3	
R7 - R8 - R9 (III sensore - <i>sensor</i>)	3	
R11 - R12 - R13 (anteriore - <i>DE</i>)	3	Termistore PT100 su cuscinetto - <i>Thermistor PT 100 on bearing</i>
R21 - R22 - R23 (posteriore - <i>NDE</i>)	3	
TB1 - TB2 (allarme- <i>warning</i>)	2	Protettore bimetallico normalmente chiuso - <i>Normally closed bi-metallic switch (**)</i>
TB3 - TB4 (intervento- <i>switch off</i>)	2	Protettore bimetallico del freno normalmente chiuso - <i>NC brake bi-metallic switch (**)</i>
TB8 - TB9 (intervento- <i>switch off</i>)	2	
TM1 - TM2 (allarme- <i>warning</i>)	2	Protettore bimetallico normalmente aperto - <i>Normally open bi-metallic switch (**)</i>
TM3 - TM4 (intervento- <i>switch off</i>)	2	
HE1- HE2	2	Resistenze riscaldanti - <i>Space heaters</i>
U1 - U2	2	Ventilazione ausiliaria monofase - <i>Single phase forced ventilation</i>
U - V - W	2	Ventilazione ausiliaria trifase - <i>Three phase forced ventilation</i>
colori secondo schema del produttore - <i>colours according manufacturer</i>	9	Encoder
CA1 - CA2	2	Condensatore - <i>Capacitor</i>
PE	1	Conduttore di terra - <i>Earth cable</i>

[*] U nominale - *U rated* = 6V - max 30V

(**) U nominale - *U rated* = 250V

FOGLIO DATI PER MOTORI ELETTRICI ASINCRONI TRIFASI : SERIE IEC
DATA SHEET FOR ASYNCHRONOUS THREEPHASE INDUCTION MOTORS: IEC SERIES

Cliente / Customer	CEMP
Offerta / Offer : 2021.	
Impianto / Plant	-

DATI DI PROGETTO - DESIGN DATA

Modo di protezione	II2G	Motore / Frame
Type of protection		Scatola morsetti / Terminal box
Tem. Amb. Min. / Min Amb.Temp.	-20 °C	
Umidità relativa / Relative humidity	90%	
Tensione nominale / Rated Voltage	400 V ± 5%	

Ex db IIB T4 Gb	IP55
Ex db IIB Gb	IP55
Tem. Amb. Max. / Max Amb. Temp.	40 °C
Altitudine / Altitude	< 1000 mslm / masl
Frequenza / Frequency	50 Hz ± 2%

DATI FUNZIONALI E COSTRUTTIVI - PERFORMANCE AND CONSTRUCTION DATA

1	Quantità / Quantity				01	
2	Motore tipo / Motor type				E3AB30 200LBX 4	
3	Numero di serie / Serial Number				-	
4	Forma costruttiva / Shape				B5	
5	Certificato / Certificate			TÜV CY	17 ATEX 0205845 X	
6	Altro certificato / Other certificate					
Dati nominali / Rated data						
7	Poli / Pole			n°	4	
8	Potenza nominale / Rated power			kW	37,00	
9	Corrente nominale / Rated current			A	67,23	
10	Velocità nominale / Full Load speed			1/min	1483	
11	Collegamento / Winding connection				D	
12	Isolamento / Insulation class				F	
13	Sovratemperatura / Temperature rise				80K	
14	Raffreddamento / Cooling type				IC411	
15	Fattore di servizio / Service factor				1	
16						
17	Classe di rendimento / Efficiency level			IEC 34-30	IE3	
Performances elettriche / Electrical performances						
Carico / Load			4/4	3/4	2/4	
18	Giri / Speed	1/min	1483	1487	1492	
19	Corr. / Curr.	A	67,23	52,59	35,21	
20	Rend / Eff	%	93,9	94,2	93,8	
21	cos φ	-	0,85	0,81	0,81	
Performances all'avviamento / Starting performances						
22	Ia/In - LRC/FLC			%	710	
23	Cosphi a rotore bloccato / LR power factor				0,37	
	Tempo a rotore bloccato / LRWT					
24	100% Un (A caldo / Warm)			sec	7	
25	(A freddo / Cold)			sec	23	
26	80% Un (A caldo / Warm)			sec	11	
27	(A freddo / Cold)			sec	36	
	Tempo di avviamento ammissibile / ART					
28	100% Un			sec	20	
29	80% Un			sec	31	
Curva di coppia / Speed-torque values						
30	Coppia nominale / Rated Torque			Nm	238,25	
31	Ca/Cn - LRT/FLT			%	220	
32	Cmax/Cn - BDT/FLT			%	280	
33						
34						
35						
Varie / Other						
36						
37						
38						
39						

Servizio / Duty		
40	Servizio / Duty type	- S1
41	Intermittenza / Cyclic duration factor	-
42	Avviamenti-ora / Starting-hour	-
43	Tempo ciclo / Time	-
Cuscinetti / Bearings		
44	Cuscinetto ant / DE bearing	- 6312 ZZ C3
45	Cuscinetto post / NDE bearing	- 6312 ZZ C3
46	Carico radiale max / Max radial load in X1	N 4350
47	Carico assiale max / Max axial load	N 1160
48	Tipo grasso / Grease type	LGHP2 SKF or equivalent
49	Intervallo lubrificazione / Lubrication	h -
50	Quantità grasso / Quantity grease	gr -
Caratteristiche meccaniche / mechanical specification		
51	Massa / Mass	kg 429,6
52	Momento d'inerzia / Moment of inertia	kgm2 0,4379
53	Rumore a vuoto / Noise at no load (1 m)	Lp dB(A) 67
54	Vibrazioni / Vibration level	IEC 34-14 A
55	Limite norma / Vibration limit	mm/sec 2,20
56		
57		
Dati entrata cavi - verniciatura / Cable entry and painting		
63	Entrata cavi / Cable entry	2xM40
64	Ciclo verniciatura / Painting cycle	STD
65	Colore finale / Final colour	RAL 5010
Ausiliari - Auxiliaries		
72	Sonde termiche / Temperature detector	winding -
73	Sonde termiche / Temperature detector	bearing -
74	Scaldiglie / Heaters	V / W -
75	Preparation for SPM sensor	-
76	Pressacavi / Cable glands	NO
77		

CURVA COPPIA/CORRENTE-GIRI
TORQUE/CURRENT-SPEED DIAGRAM

Cliente / Customer CEMP


Impianto / Plant -
ITEM -

Numero d'offerta / Offer Number 2021.
-

Motore / Motor E3AB30 200LBX 4

Potenza nominale / Rated power	37,00	kW
Poli / Pole	4	
Tensione - Frequenza / Voltage - Frequency	400 - 50	V - Hz
Corrente / Rated current	67,23	A
Velocità / Speed	1483	rpm
Coppia / Torque	238,25	Nm

— COPPIA - TORQUE — CORRENTE - CURRENT



Valori calcolati - Data obtained by calculation method

CURVA COPPIA/CORRENTE-GIRI (Tensione ridotta)
TORQUE/CURRENT-SPEED DIAGRAM (Reduced voltage)

Cliente / Customer CEMP

Impianto / Plant -
ITEM -

Numero d'offerta / Offer Number 2021.
-

Motore / Motor E3AB30 200LBX 4

Potenza nominale / Rated power 37,00 kW

Poli / Pole 4


Tensione - Frequenza / Voltage - Frequency 400 - 50 V - Hz

Corrente / Rated current 67,23 A

Velocità / Speed 1483 rpm

Coppia / Torque 238,25 Nm

— COPPIA - TORQUE — CORRENTE - CURRENT
- - - COPPIA - TORQUE 80% Un - - - CORRENTE - CURRENT 80% Un



Valori calcolati - Data obtained by calculation method


CURVE CARATTERISTICHE PERFORMANCE CURVES

Cliente / Customer CEMP

Impianto / Plant
ITEM -

Numero d'offerta / Offer Number 2021.
-

Motore / Motor	E3AB30 200LBX 4
Potenza nominale / Rated power	37,00 kW
Poli / Pole	4
Tensione - Frequenza / Voltage - Frequency	400 - 50 V - Hz
Corrente / Rated current	67,23 A
Velocità / Speed	1483 rpm
Coppia / Torque	238,25 Nm



Valori calcolati - Data obtained by calculation method

CURVA LIMITE CORRENTE TEMPO
THERMAL WITHSTAND CURVE

Cliente / Customer CEMP

Impianto / Plant -
ITEM -

Numero d'offerta / Offer Number 2021.
-

Motore / Motor E3AB30 200LBX 4

Potenza nominale / Rated power 37,00 kW


Poli / Pole 4

Tensione - Frequenza / Voltage - Frequency 400 - 50 V - Hz

Corrente / Rated current 67,23 A

Velocità / Speed 1483 rpm

Coppia / Torque 238,25 Nm



Valori calcolati - Data obtained by calculation method

CURVA LIMITE CORRENTE TEMPO (Tensione ridotta)
THERMAL WITHSTAND CURVE (Reduced voltage)

Cliente / Customer CEMP


Impianto / Plant -
ITEM -

Numero d'offerta / Offer Number 2021.
-

Motore / Motor E3AB30 200LBX 4

Potenza nominale / Rated power	37,00	kW
Poli / Pole	4	
Tensione - Frequenza / Voltage - Frequency	400 - 50	V - Hz
Corrente / Rated current	67,23	A
Velocità / Speed	1483	rpm
Coppia / Torque	238,25	Nm

— COLD (100% Un) — HOT (100% Un) - - COLD (80% Un) - - HOT (80% Un)



Valori calcolati - Data obtained by calculation method