

Nameplate Specifications

| | | | |
|----------------------------|---------|------------------------|-----------------------------|
| Output HP | 0.24 Hp | Output KW | 0.18 kW |
| Frequency | 50 Hz | Voltage | 230/400 V |
| Current | 0.80 A | Speed | 947 rpm |
| Service Factor | 1 | Phase | 3 |
| Efficiency | 63.9 % | Power Factor | 0.53 |
| Duty | S1 | Insulation Class | F |
| Frame | 71A | Enclosure | Totally Enclosed Fan Cooled |
| Ambient Temperature | 40 °C | Drive End Bearing Size | 6203 |
| Opp Drive End Bearing Size | 6203 | UL | No |
| CSA | No | CE | Yes |
| IP Code | IP55 | Number of Speeds | 1 |

Technical Specifications

| | | | |
|-----------------------|-----------------|-----------------------|----------------|
| Electrical Type | Squirrel Cage | Starting Method | Direct On Line |
| Poles | 6 | Rotation | Bi-Directional |
| Mounting | B5 | Motor Orientation | Horizontal |
| Drive End Bearing | Zz | Opp Drive End Bearing | Zz |
| Frame Material | Cast Iron | Shaft Type | Keyed |
| Overall Length | 311.00 mm | Frame Length | 112.00 mm |
| Shaft Diameter | 14.000 mm | Shaft Extension | 30 mm |
| Assembly/Box Mounting | Top | | |
| Outline Drawing | B5A048070001B01 | Connection Drawing | SC-01-T-1v-1a |