

Nameplate Specifications

| | | | |
|------------------------|----------|----------------------------|-----------------------------|
| Phase | 3 | Output HP | 475.0 Hp |
| Output KW | 355.0 kW | Voltage | 400/690 V |
| Speed | 1491 rpm | Service Factor | 1 |
| Frame | 355LC | Enclosure | Totally Enclosed Fan Cooled |
| Efficiency | 96 % | Ambient Temperature | 40 °C |
| Frequency | 50 Hz | Power Factor | 0.89 |
| Duty | S1 | Insulation Class | F |
| Drive End Bearing Size | 6322 | Opp Drive End Bearing Size | 6316 |
| UL | No | CSA | No |
| CE | Yes | IP Code | IP55 |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-----------------------|---------------|-----------------------|-----------------|
| Electrical Type | Squirrel Cage | Starting Method | Direct On Line |
| Poles | 4 | Rotation | Bi-Directional |
| Mounting | B35 | Motor Orientation | Horizontal |
| Drive End Bearing | C3 | Opp Drive End Bearing | C3 |
| Frame Material | Cast Iron | Shaft Type | Keyed |
| Overall Length | 1994.00 mm | Frame Length | 1085.00 mm |
| Shaft Diameter | 100.000 mm | Shaft Extension | 210 mm |
| Assembly/Box Mounting | Top | | |
| Connection Drawing | SC-01-T-1v-1a | Outline Drawing | B3A048350021D01 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/10/2023