

Nameplate Specifications

Phase	3	Output HP	25 Hp
Output KW	18.5 kW	Voltage	400/690 V
Speed	2944 rpm	Service Factor	1
Frame	160LA	Enclosure	Totally Enclosed Fan Cooled
Efficiency	92.4 %	Ambient Temperature	40 °C
Frequency	50 Hz	Current	32.0 A
Power Factor	0.9	Duty	S1
Insulation Class	F	Drive End Bearing Size	6309
Opp Drive End Bearing Size	6309	UL	No
CSA	Yes	CE	Yes
IP Code	IP55	Number of Speeds	1

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	2	Rotation	Bi-Directional
Mounting	B5	Motor Orientation	Horizontal
Drive End Bearing	Zz C3	Opp Drive End Bearing	Zz C3
Frame Material	Cast Iron	Shaft Type	Keyed
Overall Length	933.00 mm	Frame Length	420.00 mm
Shaft Diameter	42.000 mm	Shaft Extension	110 mm
Assembly/Box Mounting	Top		
Connection Drawing	SC-01-T-1v-1a	Outline Drawing	B5A04E8160001B01