

Nameplate Specifications

| | | | |
|----------------------------|--------|------------------------|-----------------------------|
| Output HP | 75 Hp | Output KW | 55.0 kW |
| Frequency | 50 Hz | Voltage | 400/690 V |
| Current | 93.3 A | Speed | 2981 rpm |
| Service Factor | 1 | Phase | 3 |
| Efficiency | 94.3 % | Power Factor | 0.9 |
| Duty | S1 | Insulation Class | F |
| Frame | 250MA | Enclosure | Totally Enclosed Fan Cooled |
| Ambient Temperature | 40 °C | Drive End Bearing Size | 6313 |
| Opp Drive End Bearing Size | 6313 | UL | No |
| CSA | No | CE | Yes |
| IP Code | IP55 | Number of Speeds | 1 |

Technical Specifications

| | | | |
|-----------------------|---------------|-----------------------|------------------|
| Electrical Type | Squirrel Cage | Starting Method | Direct On Line |
| Poles | 2 | Rotation | Bi-Directional |
| Mounting | B3 | Motor Orientation | Horizontal |
| Drive End Bearing | Zz C3 | Opp Drive End Bearing | Zz C3 |
| Frame Material | Cast Iron | Shaft Type | Keyed |
| Overall Length | 1197.00 mm | Frame Length | 560.00 mm |
| Shaft Diameter | 60.000 mm | Shaft Extension | 140 mm |
| Assembly/Box Mounting | Top | | |
| Connection Drawing | SC-01-T-1v-1a | Outline Drawing | B3A04E8250001A01 |