

### Nameplate Specifications

Phase	3	Output HP	25.0 Hp
Output KW	18.5 kW	Voltage	400/690 V
Speed	1477 rpm	Service Factor	1
Frame	180M	Enclosure	Totally Enclosed Fan Cooled
Efficiency	92.6 %	Ambient Temperature	40 °C
Frequency	50 Hz	Power Factor	0.83
Duty	S1	Insulation Class	F
Drive End Bearing Size	6310	Opp Drive End Bearing Size	6310
UL	No	CSA	No
CE	Yes	IP Code	IP55
Number of Speeds	1		

### Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	4	Rotation	Bi-Directional
Mounting	B35	Motor Orientation	Horizontal
Drive End Bearing	Zz C3	Opp Drive End Bearing	Zz C3
Frame Material	Cast Iron	Shaft Type	Keyed
Overall Length	934.00 mm	Frame Length	410.00 mm
Shaft Diameter	48.000 mm	Shaft Extension	110 mm
Assembly/Box Mounting	Top		
Connection Drawing	SC-01-T-1v-1a	Outline Drawing	B3A04E8185001D01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/10/2023