

PRODUCT INFORMATION PACKET

Model No: E3AC3004189B35D41100

Catalog No: E3AC3004189B35D41100

Made in Italy E3AC30 Series, General Purpose Low Voltage IEC motor IE3, Flameproof, 30,00kW,
3 phase, 1482 RPM, D400/Y690V 50Hz, 180LB Frame B35, 4 Poles, IC411, Higher Output Motor



Regal and CEMP are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E


Nameplate Specifications

Phase	3	Output HP	40.0 Hp
Output KW	30.0 kW	Voltage	400/690 V
Speed	1482 rpm	Service Factor	1
Frame	180LB	Enclosure	Totally Enclosed Fan Cooled
Efficiency	93.6 %	Ambient Temperature	40 °C
Frequency	50 Hz	Power Factor	0.85
Duty	S1	Insulation Class	F
Drive End Bearing Size	6310	Opp Drive End Bearing Size	6310
UL	No	CSA	No
CE	Yes	IP Code	IP55
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	4	Rotation	Bi-Directional
Mounting	B35	Motor Orientation	Horizontal
Drive End Bearing	Zz C3	Opp Drive End Bearing	Zz C3
Frame Material	Cast Iron	Shaft Type	Keyed
Overall Length	1008.00 mm	Frame Length	484.00 mm
Shaft Diameter	48.000 mm	Shaft Extension	110 mm
Assembly/Box Mounting	Top		
Outline Drawing	B3A04E8180001D01	Connection Drawing	SC-01-T-1v-1a

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/10/2023



CUSTOMER REFERENCE AND ADDITIONAL INFORMATION:

MOTOR TYPE AND DESCRIPTION:

DRAWING REVISION	REVISION BY	DATE	TOLERANCES (EXCEPT AS NOTED) TOLERANCES: ±2 * TOLERANCES: ±0.8 DIMENSIONS ARE IN mm ACCORDING TO IEC 60072	DRAWN BY DP	REGAL™ cemp			
ECO	APPROVED BY	DATE		DATE 29/12/2016	DESCRIPTION Motor A180 LA/LB (L) B35 IE3			
ECO DESCRIPTION COPYRIGHT CEMP Srl. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF CEMP Srl. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.				APPROVED BY DP				
				DATE 29/12/2016				
			SERIAL NUMBER	REFERENCE				
				FIRST ANGLE PROJECTION		SIZE A4	DRAWING NUMBER B3A04E8180001D01	SHEET 1 OF 2

Schema di collegamento - *Connection diagram*
Schemas de branchement - *Schaltplän*
Esquemas de conexión



DTE 01/01/2004
SC - 01 - T - 1v.doc

**Motori trifase una velocità - *Single speed, three phase motors* - Moteurs triphasé une vitesse
Drehstrommotor Eine Drehzahlstufe - Motores trifásico una velocidad**

Collegamento - *Connection* - Connexion - *Schaltung* - Conexión



Collegamento - *Connection* - Connexion - *Schaltung* - Conexión



L1 - L2 - L3 = Linea - *Supply* - Reseau - *Netz* - Red

Per invertire la rotazione invertire due fasi - *To change the rotation reverse two phases* - Pour changer le sens de rotation inverser deux phases - *Zur Drehrichtungsänderung zwei Phasen vertauschen* - Para invertir el sentido de rotación invertir dos fases

Marcatura Morsetti Ausiliari - <i>Additional terminals marking (IEC60034-8)</i>		
Marcatura <i>Marking</i>	No. morsetti <i>terminals</i>	Morsetto ausiliare per: <i>Additional terminal for:</i>
TP1A - TP2A (allarme- <i>warning</i>)	2	Termistori PTC (alta velocità) - <i>Thermistor PTC (high speed) [*]</i>
TP1B - TP2B (allarme- <i>warning</i>)	2	Termistori PTC (bassa velocità) - <i>Thermistor PTC (low speed) [*]</i>
R1 - R2 - R3 (I sensore - <i>sensor</i>)	3	Termistore PT100 3 fili - <i>Thermistor PT 100 with 3 wires</i>
R4 - R5 - R6 (II sensore - <i>sensor</i>)	3	
R7 - R8 - R9 (III sensore - <i>sensor</i>)	3	
R11 - R12 - R13 (anteriore - <i>DE</i>)	3	Termistore PT100 su cuscinetto - <i>Thermistor PT 100 on bearing</i>
R21 - R22 - R23 (posteriore - <i>NDE</i>)	3	
TB1 - TB2 (allarme- <i>warning</i>)	2	Protettore bimetallico normalmente chiuso - <i>Normally closed bi-metallic switch (**)</i>
TB3 - TB4 (intervento- <i>switch off</i>)	2	Protettore bimetallico del freno normalmente chiuso - <i>NC brake bi-metallic switch (**)</i>
TB8 - TB9 (intervento- <i>switch off</i>)	2	
TM1 - TM2 (allarme- <i>warning</i>)	2	Protettore bimetallico normalmente aperto - <i>Normally open bi-metallic switch (**)</i>
TM3 - TM4 (intervento- <i>switch off</i>)	2	
HE1- HE2	2	Resistenze riscaldanti - <i>Space heaters</i>
U1 - U2	2	Ventilazione ausiliaria monofase - <i>Single phase forced ventilation</i>
U - V - W	2	Ventilazione ausiliaria trifase - <i>Three phase forced ventilation</i>
colori secondo schema del produttore - <i>colours according manufacturer</i>	9	Encoder
CA1 - CA2	2	Condensatore - <i>Capacitor</i>
PE	1	Conduttore di terra - <i>Earth cable</i>

[*] U nominale - *U rated* = 6V - max 30V

(**) U nominale - *U rated* = 250V

FOGLIO DATI PER MOTORI ELETTRICI ASINCRONI TRIFASI : SERIE IEC
DATA SHEET FOR ASYNCHRONOUS THREEPHASE INDUCTION MOTORS: IEC SERIES

Cliente / Customer
Offerta / Offer
Impianto / Plant

DATI DI PROGETTO - DESIGN DATA

Modo di protezione	II2G	Motore / Frame
Type of protection		Scatola morsetti / Terminal box
Tem. Amb. Min. / Min Amb.Temp.	-20 °C	
Umidità relativa / Relative humidity	90%	
Tensione nominale / Rated Voltage	400 V ± 5%	

Ex db IIC T4 Gb	IP55
Ex db IIC Gb	IP55
Tem. Amb. Max. / Max Amb. Temp.	40 °C
Altitudine / Altitude	< 1000 mslm / masl
Frequenza / Frequency	50 Hz ± 2%

DATI FUNZIONALI E COSTRUTTIVI - PERFORMANCE AND CONSTRUCTION DATA

1	Quantità / Quantity		01
2	Motore tipo / Motor type		E3AC30 180LB 4
3	Numero di serie / Serial Number		-
4	Forma costruttiva / Shape		B35
5	Certificato / Certificate	TÜV CY	17 ATEX 0205845 X
6	Altro certificato / Other certificate		
Dati nominali / Rated data			
7	Poli / Pole	n°	4
8	Potenza nominale / Rated power	kW	30,00
9	Corrente nominale / Rated current	A	54,23
10	Velocità nominale / Full Load speed	1/min	1482
11	Collegamento / Winding connection		D
12	Isolamento / Insulation class		F
13	Sovratemperatura / Temperature rise		80K
14	Raffreddamento / Cooling type		IC411
15	Fattore di servizio / Service factor		1
16			
17	Classe di rendimento / Efficiency level	IEC 34-30	IE3
Performances elettriche / Electrical performances			
Carico / Load		4/4	3/4
18	Giri / Speed	1/min	1482
19	Corr. / Curr.	A	54,23
20	Rend / Eff	%	93,6
21	cos φ	-	0,85
Performances all'avviamento / Starting performances			
22	Ia/In - LRC/FLC	%	800
23	Cosphi a rotore bloccato / LR power factor		0,40
	Tempo a rotore bloccato / LRWT		
24	100% Un (A caldo / Warm)	sec	8
25	(A freddo / Cold)	sec	19
26	80% Un (A caldo / Warm)	sec	12
27	(A freddo / Cold)	sec	30
	Tempo di avviamento ammissibile / ART		
28	100% Un	sec	17
29	80% Un	sec	26
Curva di coppia / Speed-torque values			
30	Coppia nominale / Rated Torque	Nm	193,31
31	Ca/Cn - LRT/FLT	%	220
32	Cmax/Cn - BDT/FLT	%	310
33			
34			
35			
Varie / Other			
36			
37			
38			
39			


Servizio / Duty		
40	Servizio / Duty type	S1
41	Intermittenza / Cyclic duration factor	-
42	Avviamenti-ora / Starting-hour	-
43	Tempo ciclo / Time	-
Cuscinetti / Bearings		
44	Cuscinetto ant / DE bearing	6310 ZZ C3
45	Cuscinetto post / NDE bearing	6310 ZZ C3
46	Carico radiale max / Max radial load in X1	3350
47	Carico assiale max / Max axial load	880
48	Tipo grasso / Grease type	LGHP2 SKF or equivalent
49	Intervallo lubrificazione / Lubrication	h
50	Quantità grasso / Quantity grease	gr
Caratteristiche meccaniche / mechanical specification		
51	Massa / Mass	kg
52	Momento d'inerzia / Moment of inertia	kgm2
53	Rumore a vuoto / Noise at no load (1 m)	Lp dB(A)
54	Vibrazioni / Vibration level	IEC 34-14
55	Limite norma / Vibration limit	mm/sec
56		
57		
Dati entrata cavi - verniciatura / Cable entry and painting		
63	Entrata cavi / Cable entry	2xM40
64	Ciclo verniciatura / Painting cycle	STD
65	Colore finale / Final colour	RAL 5010
66		
67		
68		
69		
70		
71		
Ausiliari - Auxiliaries		
72	Sonde termiche / Temperature detector	winding
73	Sonde termiche / Temperature detector	bearing
74	Scaldiglie / Heaters	V / W
75	Preparation for SPM sensor	-
76	Pressacavi / Cable glands	NO
77		

CURVA COPPIA/CORRENTE-GIRI
TORQUE/CURRENT-SPEED DIAGRAM

Cliente / Customer -
Impianto / Plant -
ITEM -
Numero d'offerta / Offer Number -

Motore / Motor E3AC30 180LB 4
Potenza nominale / Rated power 30,00 kW
Poli / Pole 4
Tensione - Frequenza / Voltage - Frequency 400 - 50 V - Hz
Corrente / Rated current 54,23 A
Velocità / Speed 1482 rpm
Coppia / Torque 193,31 Nm

COPPIA - TORQUE CORRENTE - CURRENT



Valori calcolati - Data obtained by calculation method

Data / Date 28 January 2022

CURVA COPPIA/CORRENTE-GIRI (Tensione ridotta)
TORQUE/CURRENT-SPEED DIAGRAM (Reduced voltage)

Cliente / Customer

-

Impianto / Plant

-

ITEM

-

Numero d'offerta / Offer Number

-

-

Motore / Motor

E3AC30 180LB 4

Potenza nominale / Rated power

30,00

kW

Poli / Pole

4

Tensione - Frequenza / Voltage - Frequency

400 - 50

V - Hz

Corrente / Rated current

54,23

A

Velocità / Speed

1482

rpm

Coppia / Torque

193,31


Nm

— COPPIA - TORQUE

— CORRENTE - CURRENT

- - - COPPIA - TORQUE 80% Un


- - - CORRENTE - CURRENT 80% Un



Valori calcolati - Data obtained by calculation method

CURVE CARATTERISTICHE
PERFORMANCE CURVES

Cliente / Customer	-	
Impianto / Plant	-	
ITEM	-	
Numero d'offerta / Offer Number	-	
	-	
Motore / Motor	E3AC30 180LB 4	
Potenza nominale / Rated power	30,00	kW
Poli / Pole	4	
Tensione - Frequenza / Voltage - Frequency	400 - 50	V - Hz
Corrente / Rated current	54,23	A
Velocità / Speed	1482	rpm
Coppia / Torque	193,31	Nm




Valori calcolati - Data obtained by calculation method

Data / Date 28 January 2022

CURVA LIMITE CORRENTE TEMPO
THERMAL WITHSTAND CURVE

Cliente / Customer -
Impianto / Plant -
ITEM -
Numero d'offerta / Offer Number -

Motore / Motor	E3AC30 180LB 4	
Potenza nominale / Rated power	30,00	kW
Poli / Pole	4	
Tensione - Frequenza / Voltage - Frequency	400 - 50	V - Hz
Corrente / Rated current	54,23	A
Velocità / Speed	1482	rpm
Coppia / Torque	193,31	Nm



Valori calcolati - Data obtained by calculation method

Data / Date 28 January 2022

CURVA LIMITE CORRENTE TEMPO (Tensione ridotta)
THERMAL WITHSTAND CURVE (Reduced voltage)

Cliente / Customer -


Impianto / Plant -
ITEM -

Numero d'offerta / Offer Number -
-

Motore / Motor E3AC30 180LB 4

Potenza nominale / Rated power	30,00	kW
Poli / Pole	4	
Tensione - Frequenza / Voltage - Frequency	400 - 50	V - Hz
Corrente / Rated current	54,23	A
Velocità / Speed	1482	rpm
Coppia / Torque	193,31	Nm

— COLD (100% Un) — HOT (100% Un) - - COLD (80% Un) - - HOT (80% Un)



Valori calcolati - Data obtained by calculation method