

Nameplate Specifications

| | | | |
|----------------------------|--------|------------------------|-----------------------------|
| Output HP | 25 Hp | Output KW | 18.5 kW |
| Frequency | 50 Hz | Voltage | 400/690 V |
| Current | 36.6 A | Speed | 984 rpm |
| Service Factor | 1 | Phase | 3 |
| Efficiency | 91.7 % | Power Factor | 0.8 |
| Duty | S1 | Insulation Class | F |
| Frame | 200LA | Enclosure | Totally Enclosed Fan Cooled |
| Ambient Temperature | 40 °C | Drive End Bearing Size | 6312 |
| Opp Drive End Bearing Size | 6312 | UL | No |
| CSA | No | CE | Yes |
| IP Code | IP55 | Number of Speeds | 1 |

Technical Specifications

| | | | |
|-----------------------|------------------|-----------------------|----------------|
| Electrical Type | Squirrel Cage | Starting Method | Direct On Line |
| Poles | 6 | Rotation | Bi-Directional |
| Mounting | B3 | Motor Orientation | Horizontal |
| Drive End Bearing | Zz C3 | Opp Drive End Bearing | Zz C3 |
| Frame Material | Cast Iron | Shaft Type | Keyed |
| Overall Length | 985.00 mm | Frame Length | 460.00 mm |
| Shaft Diameter | 55.000 mm | Shaft Extension | 110 mm |
| Assembly/Box Mounting | Top | | |
| Outline Drawing | B3A04E8205001A01 | Connection Drawing | SC-01-T-1v-1a |