



Nameplate Specifications

Phase	3	Output HP	3 & 3 Hp
Output KW	2.2 & 2.2 kW	Voltage	220/380/440 & 220/380/440 V
Speed	1725 & 1425 rpm	Service Factor	1.15 & 1.15
Frame	182TCZ	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
Frequency	60 & 50 Hz	Current	8/4.6/4 & 8.2/4.7/4.1 A
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	J
UL	Recognized	CSA	Y
CE	N	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	1.5 Ohms	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Assembly/Box Mounting	F1 ONLY
Outline Drawing	OL132004	Connection Drawing	005381.01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/22/2023