

# PRODUCT INFORMATION PACKET



Model No: G801030.00  
Catalog No: G801030.00

Obsolete in the US,

replaced by 199972.00 -.40HP..1800RPM.324JM.ODP.230/460V.3PH.60HZ.CONT.40C..JM PUMP.....

Regal and Leeson are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





### Nameplate Specifications


Phase	3	Output HP	40 & 30 Hp
Output KW	30.0 & 22.4 kW	Voltage	230/460 & 190/380 V
Speed	1770 & 1475 rpm	Service Factor	1.15 & 1.0
Frame	324JM	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	93 & 93 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	97/48.5 & 88/44 A	Power Factor	82.5
Duty	Continuous	Insulation Class	B
Design Code	B	KVA Code	F
Drive End Bearing Size	6312	Opp Drive End Bearing Size	6311
UL	Recognized	CSA	Y
CE	Y	IP Code	23
Number of Speeds	1		

### Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	.165 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	JM	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	B-SS200084LE-1362	Connection Drawing	A-EE7308LE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/23/2023


B-SS2000B4LE



NOTES:

1. BOX CAN BE ROTATED IN 90° STEPS
2. BOX CAN BE MOUNTED ON OPPOSITE SIDE BY REMOVING BRACKETS AND TURNING FRAME 180°
3. NAMEPLATE TO BE READ FROM CONDUIT BOX SIDE OF MOTOR

DASH	FRAME	B	C	2F	BS	AG
1362	324JM	13.00	26.25	10.50	5.25	21.00
1512	326JM	14.50	27.75	12.00	6.00	22.50

				TOLERANCES UNLESS SPECIFIED			ELECTRIC MOTORS GEARMOTORS AND DRIVES	DRAWN NJS 02-20-2002					
				DEC.	TOLERANCE			CHK	DRS	03-27-2002			
				.X	±.1			APPD	SB	03-27-2002			
				.XX	±.03	TITLE OUTLINE - DR.PR. - CAST IRON		SCALE					
				.XXX	±.005	320JM FR. - BB - TS - D.E.V. - STL.C.BOX - TDP		REF					
				.XXXX	±.0005	✓ SURFACE ROUGHNESS UNLESS SPECIFIED	MAT'L.	FNF					
				NO.	REVISION			FINISH		PREV			
				BY	DATE	CHK	ANG	CAD FILE SS2000B4LE	SHOP BOOK	SIZE	DRAWING NO.	REV.	
				THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK. ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED. THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				DIST WA - LB - W - CA - OR - TX		B		SS2000B4LE	I