

### Nameplate Specifications

Output HP	5.0 Hp	Output KW	3.7 kW
Frequency	60 Hz	Voltage	200-230 V
Current	22.3-20.5 A	Speed	3440 rpm
Service Factor	1	Phase	1
Duty	Air Over	Insulation Class	F
Frame	184TZ	Enclosure	Open Drip Proof
Thermal Protection	No Protection	Ambient Temperature	50 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

### Technical Specifications

Electrical Type	DC Permanent Magnet	Starting Method	Across The Line
Poles	2	Rotation	Selective Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	17.38 in
Frame Length	11.50 in	Shaft Diameter	1.125 in
Shaft Extension	4.50 in		
Outline Drawing	035917CY	Connection Drawing	005368.07CY

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/27/2022