PRODUCT INFORMATION PACKET



Model No: K222M2
Catalog No: K222M2
3 HP General Purpose Motor, 1 phase, 3600 RPM, 115/230 V, 184T Frame, TEFC
General Purpose Motors



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E






Nameplate Specifications

Output HP	3 Hp	Output KW	2.2 kW
Frequency	60 Hz	Voltage	115/230 V
Current	32/16 A	Speed	3500 rpm
Service Factor	1	Phase	1
Duty	Continuous	Insulation Class	F
Frame	184T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No	Ambient Temperature	40 °C
UL	Recognized	CSA	Υ
CE	Υ	Number of Speeds	1


Technical Specifications

Electrical Type	Capacitor Start Induction Run	Starting Method	Across The Line
Poles	2	Rotation	Selective Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	14.96 in
Frame Length	9.50 in	Shaft Diameter	1.125 in
Shaft Extension	2.81 in		
Outline Drawing	035632CY	Connection Drawing	005062.01CY


This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/07/2021




VIEW FROM OUTSIDE OF MOTOR AT SWITCH END.



LINE LEADS







	ROTATION FACING LEAD END	L1	L2	JOIN
HIGH	C.C.W.	T1	T4 T5	T2,T3 T8
VOLT	C.W.	T1	T4 T8	T2,T3 T5
LOW VOLT	C.C.W.	T1,T3 T8	T2,T4 T5	
	C.W.	T1,T3 T5	T2,T4 T8	

* THIS LEAD MAY BE WHITE

				TOL UNLES	ERANCES S SPECIFIED	all all li		•		DRAWN	GR 07/23	3/12
				DEC.	INCHES		<u>Cèrtu</u>		<i></i>	снк	VS 07/23/	/ 12
				.x	±.1				APPD			
				.xx	±.01	TITLE	EXT. WIRING DIAGRAM TYPE "C" W/O PROTECTOR			SCALE	1=1	
				.xxx	±.005					REF	005062-0)1
				.xxxx	±.0005	MAT'L.	DECAL - 004012			FMF		
NO.	REVISION	BY & DATE	СНК	ANG	±1/2°	FINISH				PREV		
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT		RFP			CAD FILE	00506201CY	SIZE	DRAWING NO			REV.	
IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT — DO NOT SCALE THIS PRINT			DIST	NLV		•		\neg A	0050	62-C)1CY	