

### Nameplate Specifications

Output HP	10 Hp	Output KW	7.5 kW
Frequency	60 Hz	Voltage	230 V
Current	39 A	Speed	1715 rpm
Service Factor	1	Phase	1
Duty	Continuous Air Over	Insulation Class	F
Frame	215TZ	Enclosure	Open Drip Proof
Thermal Protection	No Protection	Ambient Temperature	50 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

### Technical Specifications

Electrical Type	DC Permanent Magnet	Starting Method	Across The Line
Poles	4	Rotation	Selective Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	21.32 in
Frame Length	12.40 in	Shaft Diameter	1.375 in
Shaft Extension	5.5 in		
Outline Drawing	K327M2-S01	Connection Drawing	D0000445-001

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/08/2022