

Nameplate Specifications

| | | | |
|-------------------------------|----------------------|----------------------------|------------------------------------|
| Output HP | 1.90 Hp | Output KW | 1.4 kW |
| Frequency | 50 Hz | Voltage | 415 V |
| Current | 4.7 A | Speed | 720 rpm |
| Phase | 3 | Duty | S4 |
| Frame | KS132MA | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Ambient Temperature | 45 °C |
| Drive End Bearing Size | 6308 ZZ | Opp Drive End Bearing Size | 6308 ZZ |
| UL | No | CSA | No |
| CE | No | IP Code | 55 |
| CDF | 100 % | Start/Hr | 6 |
| RA | 7.8 A | RV | 105 V |
| Insulation class Stator/Rotor | F/F | Temp. Rise Stator/Rotor | 75/75 K |
| Stator Connection | Delta | Rotor Connection | Star |
| Efficiency Class | Standard | | |

Technical Specifications

| | | | |
|-----------------------|-------------------------------|-----------------------|---------------------------------|
| Electrical Type | Slipring | Starting Method | Rotor resistance starter |
| Rotation | Bi-Directional | Mounting | IMB3 |
| Motor Orientation | Horizontal | Drive End Bearing | Antifriction |
| Opp Drive End Bearing | Antifriction | Frame Material | Cast Iron/Fabricated |
| Shaft Type | Single Cylinder | Overall Length | 700.00 mm |
| Frame Length | 700.00 mm | Shaft Diameter | 38.000 mm |
| Shaft Extension | 80 mm | Assembly/Box Mounting | Top |
| Rotor GD2 | 0.165 kg·m² | Pull Out Torque | 4.2 |
| Outline Drawing | CM1383 | Connection Drawing | DP1980 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:03/06/2023