

Nameplate Specifications

| | | | |
|-------------------------------|----------------------|----------------------------|------------------------------------|
| Output HP | 33.50 Hp | Output KW | 25.0 kW |
| Frequency | 50 Hz | Voltage | 415 V |
| Current | 71.0 A | Speed | 742 rpm |
| Phase | 3 | Duty | S4 |
| Frame | KS280SC | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Ambient Temperature | 45 °C |
| Drive End Bearing Size | 6317 C3 | Opp Drive End Bearing Size | 6317 C3 |
| UL | No | CSA | No |
| CE | No | IP Code | 55 |
| CDF | 60 % | Start/Hr | 600 |
| RA | 60 A | RV | 260 V |
| Insulation class Stator/Rotor | F/F | Temp. Rise Stator/Rotor | 75/75 K |
| Stator Connection | Delta | Rotor Connection | Star |
| Efficiency Class | Standard | | |

Technical Specifications

| | | | |
|-----------------------|------------------------|-----------------------|---------------------------------|
| Electrical Type | Slipring | Starting Method | Rotor resistance starter |
| Rotation | Bi-Directional | Mounting | IMB3 |
| Motor Orientation | Horizontal | Drive End Bearing | Antifriction |
| Opp Drive End Bearing | Antifriction | Frame Material | Cast Iron/Fabricated |
| Shaft Type | Single Cylinder | Overall Length | 1300.00 mm |
| Frame Length | 1300.00 mm | Shaft Diameter | 75.000 mm |
| Shaft Extension | 140 mm | Assembly/Box Mounting | Top |
| Rotor GD2 | 12.7 kg·m² | Pull Out Torque | 5.4 |
| Connection Drawing | DP3050 | Outline Drawing | cm5906 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:03/06/2023