

## Nameplate Specifications

|                               |               |                            |                             |
|-------------------------------|---------------|----------------------------|-----------------------------|
| Output HP                     | 4.40 Hp       | Output KW                  | 3.3 kW                      |
| Frequency                     | 50 Hz         | Voltage                    | 415 V                       |
| Current                       | 6.7 A         | Speed                      | 925 rpm                     |
| Phase                         | 3             | Duty                       | S3                          |
| Frame                         | KS132MA       | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection            | No Protection | Ambient Temperature        | 45 °C                       |
| Drive End Bearing Size        | 6308 ZZ       | Opp Drive End Bearing Size | 6308 ZZ                     |
| UL                            | No            | CSA                        | No                          |
| CE                            | No            | IP Code                    | 55                          |
| CDF                           | 25 %          | Start/Hr                   | 300                         |
| RA                            | 14.4 A        | RV                         | 115 V                       |
| Insulation class Stator/Rotor | F/F           | Temp. Rise Stator/Rotor    | 75/75 K                     |
| Stator Connection             | Delta         | Rotor Connection           | Star                        |
| Efficiency Class              | Standard      |                            |                             |

## Technical Specifications

|                       |                 |                       |                          |
|-----------------------|-----------------|-----------------------|--------------------------|
| Electrical Type       | Slipring        | Starting Method       | Rotor resistance starter |
| Rotation              | Bi-Directional  | Mounting              | IMB3                     |
| Motor Orientation     | Horizontal      | Drive End Bearing     | Antifriction             |
| Opp Drive End Bearing | Antifriction    | Frame Material        | Cast Iron/Fabricated     |
| Shaft Type            | Single Cylinder | Overall Length        | 700.00 mm                |
| Frame Length          | 700.00 mm       | Shaft Diameter        | 38.000 mm                |
| Shaft Extension       | 80 mm           | Assembly/Box Mounting | Top                      |
| Rotor GD2             | 0.16 kg·m²      | Pull Out Torque       | 2                        |
| Outline Drawing       | CM1383          | Connection Drawing    | DP1949                   |

