

## Nameplate Specifications

|                               |               |                            |                             |
|-------------------------------|---------------|----------------------------|-----------------------------|
| Output HP                     | 12.70 Hp      | Output KW                  | 9.5 kW                      |
| Frequency                     | 50 Hz         | Voltage                    | 415 V                       |
| Current                       | 25.5 A        | Speed                      | 977 rpm                     |
| Phase                         | 3             | Duty                       | S5                          |
| Frame                         | KS180L1       | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection            | No Protection | Ambient Temperature        | 45 °C                       |
| Drive End Bearing Size        | 6310 ZZ       | Opp Drive End Bearing Size | 6310 ZZ                     |
| UL                            | No            | CSA                        | No                          |
| CE                            | No            | IP Code                    | 55                          |
| CDF                           | 60 %          | Start/Hr                   | 300                         |
| RA                            | 25 A          | RV                         | 230 V                       |
| Insulation class Stator/Rotor | F/F           | Temp. Rise Stator/Rotor    | 75/75 K                     |
| Stator Connection             | Delta         | Rotor Connection           | Star                        |
| Efficiency Class              | Standard      |                            |                             |

## Technical Specifications

|                       |                 |                       |                          |
|-----------------------|-----------------|-----------------------|--------------------------|
| Electrical Type       | Slipring        | Starting Method       | Rotor resistance starter |
| Rotation              | Bi-Directional  | Mounting              | IMB3                     |
| Motor Orientation     | Horizontal      | Drive End Bearing     | Antifriction             |
| Opp Drive End Bearing | Antifriction    | Frame Material        | Cast Iron/Fabricated     |
| Shaft Type            | Single Cylinder | Overall Length        | 875.00 mm                |
| Frame Length          | 875.00 mm       | Shaft Diameter        | 48.000 mm                |
| Shaft Extension       | 110 mm          | Assembly/Box Mounting | Top                      |
| Rotor GD2             | 1.3 kg·m²       | Pull Out Torque       | 5.3                      |
| Connection Drawing    | DP2170          | Outline Drawing       | CM1383                   |

