

PRODUCT INFORMATION PACKET

Model No: LM01285

Catalog No: LM01285

OBSOLETE - REPLACED BY LM33088 - 3,1800,TEFC,182T,3/60/200/400

Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E



Nameplate Specifications

Output HP	3 Hp	Output KW	2.2 kW
Frequency	60 Hz	Voltage	200/400 V
Current	9.8/4.9 A	Speed	1735 rpm
Service Factor	1.15	Phase	3
Efficiency	82.5 %	Power Factor	78.6
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	J
Frame	182T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	207	Opp Drive End Bearing Size	205
UL	Recognized	CSA	Y
CE	Y	IP Code	43
Number of Speeds	1		


Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	6.96 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Aluminum
Shaft Type	T	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	B-SS601006LN-620	Connection Drawing	A-EE7308-LN

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:07/18/2022

NOTES:

1. CONDUIT BOX BE ROTATED IN 90° STEPS.
2. NAMEPLATE TO BE READ FROM CONDUIT BOX SIDE OF MOTOR.

DASH	FR.	C	BS	B	2FF	2F	FOOT HOLE	12	REVISED "B" DIMENSION IN DASH TABLE	ECN 14167	MSG 8/19/2009	BW	TOLERANCES UNLESS SPECIFIED		DRAWN BLR 01-13-2000			
								11	DE EXTN WAS 3.1 CHANGED TO 3.0		SVL 7/22/2009	ML	DEC.		INCHES	CHK ML 01-18-2000		
								10	REVISED DASH TABLE INFORMATION	CN 32829	DRS 09-10-2004	ML	.X		±.1	APPD GK 01-18-2000		
620	182T	14.19	2.25	6.30	4.50	---	4	9	REVISED -820, 2FF WAS 5.50 & 2F WAS BLANK		TAT 06-23-2004	ML	.XX		±.03	SCALE 7=16		
720	182/4T	15.19	2.75	7.30	5.50	4.50	8	8	RE-ISSUE CLARIFIED HOLES		TAT 01-30-2004	ML	.XXX		±.005	REF		
720	184T	15.19	2.75	7.30	5.50	---	4	7	CHANGED 2F TO 2FF		TAT 01-27-2004	ML	.XXXX	±.0005	MAT'L	FMF		
								NO.	REVISION		BY & DATE	CHK	ANG	±1/2"	FINISH	PREV		
820	184T	16.19	3.25	8.30	---	5.50	8	THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				RFST	DFT	CAD FILE ss601006Ln	SIZE B	DRAWING NO. SS601006LN	PAGE OF 12	REV. 12

THREE PHASE
DUAL VOLTAGE MOTOR

HIGH VOLTAGE



LOW VOLTAGE



VIEW OF TERMINAL END

REF.
WINDING DIAGRAM

T8Y, T2Y, T2BL, T4BX, T2EC, T2G
T6BZ, T2B, T6BL, T4AV, T6B, T4B

OPTIONAL CORD
CONNECTION

L1 — WHITE
L2 — RED
L3 — BLACK

				TOLERANCES UNLESS SPECIFIED			DRAWN BLR 06/11/1999			
				DEC.	INCHES		CHK ML 06/18/1999			
				.X	±.1		APPD GK 06/18/1999			
3	ADDED THE OPTIONAL CORD CONNECTION MU46318	RDH 04/24/2003	DRS	.XX	±.02	TITLE CONNECTION DIAGRAM 3ø – DUAL VOLTAGE MOTOR	SCALE 1=1			
2	RE-ISSUE, ADDED '-' TO PART NUMBER	BLR 08/09/1999	GK	.XXX	±.005		REF			
1	NEW DRAWING	BLR 06/18/1999	GK	.XXXX	±.0005	MAT'L.	FMF			
NO.	REVISION	BY & DATE	CHK	ANG	±7'30"	FINISH	PREV			
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT – DO NOT SCALE THIS PRINT				RFP		CAD FILE EE7308LN	SIZE	DRAWING NO.	PAGE OF	REV.
				DIST WP			A	EE7308-LN		3