

Nameplate Specifications

| | | | |
|------------------------|------------|----------------------------|---------------------------------|
| Output HP | 3CHP Hp | Output KW | 2.2 kW |
| Frequency | 60 Hz | Voltage | 230/460 V |
| Current | 8.4/4.2 A | Speed | 1755 rpm |
| Service Factor | 1.15 | Phase | 3 |
| Efficiency | 85.5 % | Power Factor | 80 |
| Duty | Continuous | Insulation Class | F |
| Design Code | B | KVA Code | P |
| Frame | 184TC | Enclosure | Totally Enclosed Non Ventilated |
| Thermal Protection | Thermostat | Ambient Temperature | 40 °C |
| Drive End Bearing Size | 207 | Opp Drive End Bearing Size | 205 |
| UL | Recognized | CSA | Y |
| CE | Y | IP Code | 43 |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-----------------------|-----------------------------|-----------------------|------------------|
| Electrical Type | Squirrel Cage Inverter Duty | Starting Method | Inverter Only |
| Poles | 4 | Rotation | Reversible |
| Resistance Main | 3.55 Ohms | Mounting | Rigid Base |
| Motor Orientation | Horizontal | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Aluminum |
| Shaft Type | T | Assembly/Box Mounting | F1/F2 CAPABLE |
| Inverter Load | CONSTANT 2000:1 | | |
| Connection Drawing | A-EE7308T-LN | Outline Drawing | B-SS601040LN-720 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:07/18/2022