

Nameplate Specifications

Output HP	30 Hp	Output KW	22.4 kW
Frequency	60 Hz	Voltage	200/400 V
Current	86.0/43.0 A	Speed	1765 rpm
Service Factor	1.15	Phase	3
Efficiency	88.5 %	Power Factor	84
Duty	Continuous	Insulation Class	F
Design Code	A	KVA Code	J
Frame	286T	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	310	Opp Drive End Bearing Size	209
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Wye Start Delta Run
Poles	4	Rotation	Reversible
Mounting	Rigid Base	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	T
Assembly/Box Mounting	F1/F2 CAPABLE		
Connection Drawing	A-EE7308AA-LN	Outline Drawing	XF1D1SS1-1448

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:07/18/2022