



Nameplate Specifications

| | | | |
|------------------------|-------------------|----------------------------|-----------------------------|
| Phase | 3 | Output HP | 3 & 3 Hp |
| Output KW | 2.2 & 2.2 kW | Voltage | 230/460 & 380-415 V |
| Speed | 1170 & 975 rpm | Service Factor | 1.25 & 1.15 |
| Frame | 213TC | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Efficiency | 89.5 & 87.5 % |
| Ambient Temperature | 40 °C | Frequency | 60 & 50 Hz |
| Current | 8.8/4.4 & 5.5-5 A | Power Factor | 70 |
| Duty | Continuous | Insulation Class | F |
| Design Code | B | KVA Code | K |
| Drive End Bearing Size | 208 | Opp Drive End Bearing Size | 206 |
| UL | Recognized | CSA | Y |
| CE | Y | IP Code | 43 |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-----------------------|-----------------------------|-----------------------|------------------|
| Electrical Type | Squirrel Cage Induction Run | Starting Method | Across The Line |
| Poles | 6 | Rotation | Reversible |
| Resistance Main | 2.785 Ohms | Mounting | Rigid Base |
| Motor Orientation | Horizontal | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Aluminum |
| Shaft Type | T | Overall Length | 19.57 in |
| Frame Length | 9.50 in | Shaft Diameter | 1.375 in |
| Shaft Extension | 3.12 in | Assembly/Box Mounting | F1/F2 CAPABLE |
| Connection Drawing | A-EE7308-LN | Outline Drawing | B-SS330102LN-950 |