

Nameplate Specifications

| | | | |
|------------------------|---------------|----------------------------|------------|
| Output HP | 5 Hp | Output KW | 3.7 kW |
| Frequency | 60 Hz | Voltage | 230/460 V |
| Current | 13.2/6.6 A | Speed | 1745 rpm |
| Service Factor | 1 | Phase | 3 |
| Efficiency | 87.5 % | Power Factor | 81 |
| Duty | Continuous | Insulation Class | F |
| Design Code | B | KVA Code | J |
| Frame | 184T | Enclosure | Drip Proof |
| Thermal Protection | No Protection | Ambient Temperature | 40 °C |
| Drive End Bearing Size | 206 | Opp Drive End Bearing Size | 203 |
| UL | No | CSA | Y |
| IP Code | 12 | Number of Speeds | 1 |

Technical Specifications

| | | | |
|-----------------------|-----------------------------|-----------------------|-----------------|
| Electrical Type | Squirrel Cage Induction Run | Starting Method | Across The Line |
| Poles | 4 | Rotation | Reversible |
| Resistance Main | 3.2 Ohms | Mounting | Rigid Base |
| Motor Orientation | Horizontal | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Rolled Steel |
| Shaft Type | T | Assembly/Box Mounting | F1/F2 CAPABLE |
| Connection Drawing | A-EE7308-LN | Outline Drawing | A-SS69222LN-725 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:07/18/2022