



Nameplate Specifications

| | | | |
|------------------------|----------------------|----------------------------|--|
| Output HP | 1.50 Hp | Output KW | 1.1 kW |
| Frequency | 60 Hz | Voltage | 460 V |
| Current | 2.2 A | Speed | 1175 rpm |
| Service Factor | 1 | Phase | 3 |
| Efficiency | 86.5 % | Power Factor | 71.5 |
| Duty | Continuous | Insulation Class | F |
| Design Code | B | KVA Code | L |
| Frame | 184UC | Enclosure | Totally Enclosed Non Ventilated |
| Thermal Protection | No Protection | Ambient Temperature | 65 °C |
| Drive End Bearing Size | 207 | Opp Drive End Bearing Size | 205 |
| UL | Recognized | CSA | Y |
| CE | Y | IP Code | 43 |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-----------------------|------------------------------------|-----------------------|------------------------|
| Electrical Type | Squirrel Cage Induction Run | Starting Method | Across The Line |
| Poles | 6 | Rotation | Reversible |
| Resistance Main | 7.75 Ohms | Mounting | Rigid Base |
| Motor Orientation | Horizontal | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Cast Iron |
| Shaft Type | U | Assembly/Box Mounting | F1/F2 CAPABLE |
| Connection Drawing | A-EE7300-LN | Outline Drawing | A-SS69028LN-675 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:03/30/2023