

Nameplate Specifications

Output HP	200,50 Hp	Output KW	149.0 kW
Frequency	60 Hz	Voltage	460 V
Current	230,101 A	Speed	1785,895 rpm
Service Factor	1.15	Phase	3
Efficiency	95.4 %	Power Factor	85.5
Duty	Continuous	Insulation Class	F
Design Code	1VT	KVA Code	J
Frame	445T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6318	Opp Drive End Bearing Size	6315
UL	Recognized	CSA	Y
CE	Y	IP Code	43
Number of Speeds	2		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4/8	Rotation	Reversible
Resistance Main	.02178 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F1 ONLY
Outline Drawing	XK2FACSS1-2317	Connection Drawing	EE7322D-LN

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/10/2022