

Product Information Packet: Model No: LM21192, Catalog No:LM21192 Speed Ratio Motors, TEFC, 5 HP, 3 Ph, 60 Hz, 230/460 V, 3475 RPM, 184T Frame

Nameplate Specifications

Output HP	5 Hp	Output KW	3.7 kW
Frequency	60 Hz	Voltage	230/460 V
Current	12.4/6.2 A	Speed	3475 rpm
Service Factor	1.15	Phase	3
Efficiency	87.5 %	Power Factor	88
Duty	Continuous	Insulation Class	F
Design Code	INV	KVA Code	J
Frame	184T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	207	Opp Drive End Bearing Size	205
UL	Recognized	CSA	Y
CE	Y	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Duty	Starting Method	Inverter Only
Poles	2	Rotation	Reversible
Resistance Main	2.12 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Aluminum
Shaft Type	T	Overall Length	15.19 in
Frame Length	7.30 in	Shaft Diameter	1.125 in
Shaft Extension	2.75 in	Assembly/Box Mounting	F1/F2 CAPABLE
Inverter Load	CONSTANT 4:1		
Connection Drawing	A-EE7308T-LN	Outline Drawing	B-SS601006LN-720

