

### Nameplate Specifications

Output HP	60 Hp	Output KW	45.0 kW
Frequency	60 Hz	Voltage	460 V
Current	67.5 A	Speed	1780 rpm
Service Factor	1	Phase	3
Efficiency	95 %	Power Factor	87.5
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	G
Frame	405U	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	65 °C
Drive End Bearing Size	316	Opp Drive End Bearing Size	313
UL	Recognized	CSA	Y
CE	Y	IP Code	43
Number of Speeds	1		

### Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	.095 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	U	Overall Length	37.00 in
Frame Length	16.75 in	Shaft Diameter	2.375 in
Shaft Extension	7.12 in	Assembly/Box Mounting	F1/F2 CAPABLE
Connection Drawing	A-EE7300U-LN	Outline Drawing	B-SS514649LN-1675