

PRODUCT INFORMATION PACKET

Model No: LM21866

Catalog No: LM21866

Automotive Duty Motor, 60 HP, 3 Ph, 60 Hz, 460 V, 1800 RPM, 405UC Frame, TEFC







Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

Nameplate Specifications

Output HP	60 Hp	Output KW	45.0 kW
Frequency	60 Hz	Voltage	460 V
Current	67.5 A	Speed	1780 rpm
Service Factor	1	Phase	3
Efficiency	95 %	Power Factor	87.5
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	G
Frame	405UC	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	65 °C
Drive End Bearing Size	6316	Opp Drive End Bearing Size	6313
UL	Recognized	CSA	Y
CE	Y	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	.095 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	U	Overall Length	37.01 in
Frame Length	16.75 in	Shaft Diameter	2.375 in
Shaft Extension	6.88 in	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	B-SS551924LN-1675	Connection Drawing	A-EE7300U-LN



VIEW OF TERMINAL END

				TOLERANCES UNLESS SPECIFIED			DRAWN KL 12-06-2000					
				DEC.	INCHES		CHK DJK 12-06-2000					
				.X	±.1		APPD DJK 12-06-2000					
				.XX	±.02		SCALE					
2	ADDED TABLES	CN39272	RJW 06-03-2005	ML	.XXX	±.005	TITLE EXTERNAL CONNECTION DIAGRAM					
1	NEW DRAWING	MU34873	KL 12-06-2000		.XXXX	±.0005	3Ø SINGLE VOLTAGE DELTA					
NO.	REVISION	BY & DATE	CHK	ANG	±7'30"		REF					
						FINISH	FMF					
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				RFP	CAD FILE EE7300U_LN			SIZE	DRAWING NO.	PAGE	OF	REV.
				DIST LE		A	EE7300U-LN	2				



**2100 WASHINGTON ST.
GRAFTON, WI
PH. 262-277-8810**

CONN. DIAGRAM: A-EE7300U-LN

OUTLINE: B-SS551924LN-1675

CATALOG #: LM21866

WINDING #: T4054125 1

MOUNTING: F1/F2 CAPABLE

TYPICAL MOTOR PERFORMANCE DATA

HP	kW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
60	45.0	1800	1780	405UC	TEFC	G	B

PH	Hz	VOLTS	AMPS	START TYPE	DUTY	INSL	S.F.	AMB°C
3	60	460	67.5	ACROSS THE LINE	CONTINUOUS	F1	1.0	65

FULL LOAD EFF:	95	3/4 LOAD EFF:	95	1/2 LOAD EFF:	94.5	GTD. EFF	94.5	ELEC. TYPE	SQ CAGE IND RUN
FULL LOAD PF:	87.5	3/4 LOAD PF:	85	1/2 LOAD PF:	79				

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B.D. TORQUE	F.L. RISE°C
177 LB-FT	435	255 LB-FT 144 %	440 LB-FT 249 %	48

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS / HOUR	APPROX. MOTOR WGT
66 dBA	76 dBA	23 LB-FT^2	- LB-FT^2	30 SEC.	-	1100 LBS.

***** SUPPLEMENTAL INFORMATION *****

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
C-FACE	STANDARD	RIGID	HORIZONTAL	FALSE	NONE	FALSE	NONE	GRAY - LINCOLN

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	ODE	POLYREX EM	U	NONE	NONE	1045 HOT ROLLED (C-204)	CAST IRON
BALL	BALL						
6316	6313						

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs	NONE	FALSE	NONE VOLTS
NONE	NOT	NONE	NONE			

*
N
O
T
E
S
*

INVERTER TORQUE: NONE
INV. HP SPEED RANGE: NONE
ENCODER: NONE NONE NONE NONE NONE PPR
BRAKE: NONE NONE NONE P/N NONE NONE NONE NONE FT-LB NONE V NONE Hz

Data Sheet

Date: 1/23/2018

LM21866



Data @ **460 V**


Motor Load Data

Load	0%	25%	50%	75%	100%	115%	125%	LR
Current (Amps)	19.5	25.5	37.5	52.0	67.5	77.5	84.5	435
Torque (ft-lb)	0.00	44.0	88.0	132	177	204	222	255
RPM	1800	1795	1790	1785	1780	1.778	1775	0
Efficiency (%)		91.7	94.5	95.0	95.0	94.5	94.1	
P.F. (%)	4.5	59.0	79.0	85.0	87.5	88.0	88.0	25.0

Motor Speed Data

	LR	Pull-Up	BD	Rated	Idle
Speed (RPM)	0	900	1700	1780	1800
Current (Amps)	435	400	250	67.5	19.5
Torque (ft-lb)	255	225	440	177	0.00

Information Block				
HP	60.0			
Sync. RPM	1800			
Frame	404			
Enclosure	TEFC			
Construction	TFS			
Voltage	460 V			
Frequency	60 Hz			
Design	A			
LR Code letter	G			
Service Factor	1.15			
Temp Rise @ FL	48 °C			
Duty	CONT			
Ambient	40 °C			
Elevation	1,000 feet			
Rotor/Shaft wk ²	23.0 Lb-Ft ²			
Ref Wdg	T4054125 NONE			
Sound Pressure @ 1M	75 dBA			
VFD Rating	NONE			
Outline Dwg	B-SS551924LN-1675			
Conn. Diag	A-EE7300U-LN			
Additional Specifications:				
0				
0				
EQUIV CKT (OHMS / PHASE)				
R1	R2	X1	X2	Xm
0.0600	0.0410	0.4720	0.3860	13.2440



Speed - Torque Curve

