



Nameplate Specifications

| | | | |
|------------------------|-----------------|----------------------------|---------------------|
| Phase | 1 | Output HP | 10 & 15 Hp |
| Output KW | 7.5 & 11.2 kW | Voltage | 230 & 230 V |
| Speed | 3495 & 3450 rpm | Service Factor | 1.5 & 1.0 |
| Frame | 215TZ | Enclosure | Drip Proof Air Over |
| Thermal Protection | No Protection | Efficiency | 82.5 & 82.5 % |
| Ambient Temperature | 40 °C | Frequency | 60 & 60 Hz |
| Current | 46 & 71 A | Power Factor | 83.5 |
| Duty | Continuous | Insulation Class | F |
| Design Code | NO DESIGN CODE | KVA Code | C |
| Drive End Bearing Size | 307 | Opp Drive End Bearing Size | 206 |
| UL | Recognized | CSA | Y |
| CE | N | IP Code | 22 |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-----------------------|-------------------------------|-----------------------|----------------------------|
| Electrical Type | Capacitor Start Induction Run | Starting Method | Across The Line |
| Poles | 2 | Rotation | Selective Counterclockwise |
| Resistance Main | .151 Ohms | Mounting | Rigid Base |
| Motor Orientation | Horizontal | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Rolled Steel |
| Shaft Type | Single Special Extension | Overall Length | 18.16 in |
| Frame Length | 11.15 in | Shaft Diameter | 1.125 in |
| Shaft Extension | 3.5 in | Assembly/Box Mounting | F1 ONLY |
| Outline Drawing | A-SS86663LN-1115 | Connection Drawing | A-EE7090JM-LN |