



Nameplate Specifications

Phase	3	Output HP	5 & 10 Hp
Output KW	3.7 & 7.5 kW	Voltage	110 & 220 V
Speed	1760 & rpm	Service Factor	1.0 & 1.0
Frame	184T	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	87.5 %
Ambient Temperature	40 °C	Frequency	60 & 120 Hz
Current	27.6 & 27.6 A	Power Factor	81.1
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	J
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	N	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	3.17 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F1 ONLY
Outline Drawing	035693-900	Connection Drawing	005102.01ME

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/22/2023