



Nameplate Specifications

Phase	3	Output HP	15 & 15 Hp
Output KW	11.2 & 11.2 kW	Voltage	230/460 & 190-208/380-415 V
Speed	1770 & 1455 rpm	Service Factor	1.25 & 1.0
Frame	254TC	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	93 & 91 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	38.5/19.2 & 46-44/23-22 A	Power Factor	78.5
Duty	Continuous	Insulation Class	F
Design Code	A	KVA Code	J
Drive End Bearing Size	309	Opp Drive End Bearing Size	208
UL	Recognized	CSA	Y
CE	Y	IP Code	12
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	.48 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	NEMA STD DBL	Assembly/Box Mounting	F1-DE-BOX
Outline Drawing	B-SS203950LN-1515	Connection Drawing	A-EE7308-LN

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/22/2023