

Nameplate Specifications

Output HP	20 Hp	Output KW	14.9 kW
Frequency	30 Hz	Voltage	200 V
Current	62.0 A	Speed	880 rpm
Service Factor	1	Phase	3
Efficiency	91 %	Power Factor	75.5
Duty	Elevator	Insulation Class	F
Design Code	INV	KVA Code	L
Frame	324TC	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	311	Opp Drive End Bearing Size	309
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Duty	Starting Method	Wye Start Delta Run Or Inverter
Poles	4	Rotation	Reversible
Resistance Main	.55 Ohms	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Overall Length	29.30 in
Frame Length	15.63 in	Shaft Diameter	2.125 in
Shaft Extension	5.3 in	Assembly/Box Mounting	F1/F2 CAPABLE
Connection Drawing	A-EE7340D-LN	Outline Drawing	XG3D1EC33B-1507