



Nameplate Specifications

Phase	1	Output HP	10 & 15 Hp
Output KW	7.5 & 11.2 kW	Voltage	200-230 & 200-230 V
Speed	3550 & 3500 rpm	Service Factor	1.0 & 1.0
Frame	215TCV	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	88.5 & 86.5 %
Ambient Temperature	40 °C	Frequency	60 & 60 Hz
Current	43.5-38 & 71.5-60 A	Power Factor	94.5
Duty	VERIFY	Insulation Class	F
Design Code	L	KVA Code	E
Drive End Bearing Size	309	Opp Drive End Bearing Size	206
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	2	Rotation	Selective Counterclockwise
Resistance Main	136 Ohms	Mounting	Round
Motor Orientation	Shaft Down	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	037661LN-1240	Connection Drawing	EE9048MG-LN

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/22/2023