



Nameplate Specifications

Phase	3	Output HP	30 & 40 Hp
Output KW	22.4 & 30.0 kW	Voltage	230/460 & 230/460 V
Speed	1770 & 1770 r/min	Service Factor	1.0 & 1.0
Frame	286T	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	92.4 & 91.7 %
Ambient Temperature	40 °C	Frequency	60 & 60 Hz
Current	72/36 & 97/48.5 A	Power Factor	84
Duty	120/80 Starts/Hour	Insulation Class	F
Design Code	INV	KVA Code	D
Drive End Bearing Size	6311	Opp Drive End Bearing Size	6210
UL	Recognized	CSA	Y
CE	Y	IP Code	12
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Wye Start Delta Run
Poles	4	Rotation	Reversible
Resistance Main	.295 O	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Overall Length	24.99 in
Frame Length	14.25 in	Shaft Diameter	1.875 in
Shaft Extension	4.63 in	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	SS200030LN-1425	Connection Drawing	EE7358-LN