



### Nameplate Specifications

Output HP	5 Hp	Output KW	3.7 kW
Frequency	60 Hz	Voltage	230/460 V
Current	16.2/8.1 A	Speed	1150 rpm
Service Factor	1.15	Phase	3
Efficiency	82.5 %	Power Factor	70
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	H
Frame	215TCVZ	Enclosure	Totally Enclosed Air Over
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6208	Opp Drive End Bearing Size	6206
UL	Recognized	CSA	Y
CE	Y	IP Code	43
Number of Speeds	1		

### Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	6	Rotation	Reversible
Resistance Main	2.66 Ohms	Mounting	Rigid Base
Motor Orientation	Shaft Down	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Aluminum
Shaft Type	Single Special Extension	Shaft Diameter	1.375 in
Assembly/Box Mounting	W6	Inverter Load	VARIABLE 10:1
Connection Drawing	A-EE7308-LN	Outline Drawing	SS330141A-950

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:03/23/2023