

Nameplate Specifications

Output HP	10 Hp	Output KW	7.5 kW
Frequency	60 Hz	Voltage	230 V
Current	39.0 A	Speed	1745 rpm
Service Factor	1.25	Phase	1
Efficiency	87.5 %	Power Factor	95.5
Duty	Continuous	Insulation Class	F
Design Code	L	KVA Code	H
Frame	215TZ	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6309	Opp Drive End Bearing Size	6206
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	4	Rotation	Selective Counterclockwise
Resistance Main	0 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Shaft Diameter	1.375 in
Assembly/Box Mounting	F1 ONLY		
Connection Drawing	EE9048LX-LN	Outline Drawing	OLLM32305-1240