



### Nameplate Specifications

Phase	3	Output HP	20 Hp
Output KW	14.9 kW	Voltage	200 V
Speed	1758 rpm	Service Factor	1.00
Frame	256TCZ	Enclosure	Totally Enclosed Air Over
Thermal Protection	Thermostat	Efficiency	91 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	61.0 A	Power Factor	77
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	M
Drive End Bearing Size	6309	Opp Drive End Bearing Size	6206
UL	Recognized	CSA	Y
CE	N	IP Code	43
Number of Speeds	1		

### Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	WYE RUN DELTA BOOST
Poles	4	Rotation	Reversible
Resistance Main	0 Ohms	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Aluminum
Shaft Type	Special Extension Both Sides	Shaft Diameter	1.625 in
Assembly/Box Mounting	F1/F2 CAPABLE		
Outline Drawing	B-SS330256LN-1150	Connection Drawing	A-EE7304AE-LN