

## Nameplate Specifications

Output HP	30 Hp	Output KW	22.4 kW
Frequency	60 Hz	Voltage	230 V
Current	69.0 A	Speed	3600 rpm
Service Factor	1	Phase	3
Efficiency	91.6 %	Power Factor	88
Duty	Continuous	Insulation Class	F
Design Code	PC	KVA Code	None
Frame	286TZ	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6311	Opp Drive End Bearing Size	6210
UL	No	CSA	N
CE	N	IP Code	43
Number of Speeds	1		

## Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Resistance Main	.195 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	Single Special Extension	Assembly/Box Mounting	F1/F2 CAPABLE
Connection Drawing	A-EE7300U-LN	Outline Drawing	B-SS301451LN-1425

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/10/2022