



**Nameplate Specifications**

Phase	3	Output HP	15 & 15 Hp
Output KW	11.2 & 11.2 kW	Voltage	230/460 & 190/380 V
Speed	1770 & 1462 rpm	Service Factor	1.25 & 1.25
Frame	254TV	Enclosure	Totally Enclosed Air Over
Thermal Protection	No Protection	Efficiency	91 & 90.2 %
Ambient Temperature	-40 °C	Frequency	60 & 50 Hz
Current	39/19.5 & 45.5/22.7 A	Power Factor	80
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	G
Drive End Bearing Size	6309	Opp Drive End Bearing Size	6208
UL	Recognized	CSA	Y
CE	N	IP Code	43
Number of Speeds	1		

**Technical Specifications**

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	.575 Ohms	Mounting	Rigid Base
Motor Orientation	Shaft Down	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Aluminum
Shaft Type	T	Assembly/Box Mounting	W6
Outline Drawing	B-SS321178LN-1375	Connection Drawing	A-EE7308-LN

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/23/2023